




RoHS COMPLIANT

100+10/-5mm

A-A



WIRING:T568B		
PLUG	KEYSTONE JACK	COLOR
PIN1	PIN1	WHITE/ORANGE
PIN2	PIN2	ORANGE
PIN3	PIN3	WHITE/GREEN
PIN6	PIN6	GREEN
PIN4	PIN4	BLUE
PIN5	PIN5	WHITE/BLUE
PIN7	PIN7	WHITE/BROWN
PIN8	PIN8	BROWN
SHIELDED	SHIELDED	DRAIN WIRE

⑫	Metal Foil	Copper	10x35MM	1	ZFCUDBXX
⑪	Screw	Steel	2.6X4.5MM	1	SAS3X4.500SBB21X
⑩	MOLDING	PVC	60Pa	1	PLPVCXXXXXX60
⑨	Insert1	PC	-----	1	PG88X2000XY0-1-IH3
	PLUG	PC	8P8C "BN"Marking 6U"	1	PG88XfJ0BXS0
⑧	MOLDING	PVC	60Pa	1	PLPVCXXXXXX60 ZSRXXX131
⑦	Housing	ABS	Nickel plated on the surface	1	AH0115XIXXXX
				1	AH0115XDXXXX-S
				1	AH0115XUXXXX-S
⑥	IDC Housing	PC	KRONE IDC TYPE WH(BN:D8)	2	AHIDCX4ZXXXX-02
⑤	IDC Terminal	PHOSPHOR COPPER	-----	8	NIDBN
④	Label	PAPER	6.8X16.2	1	KLKSXXX02
③	Cable	PVC	FTP CAT.6 26AWG(7X0.16)	1	TC8C26XXXCXX547
②	PCB	FR-4	1.6mm	1	ZPSPJCAT6X
①	Modular jack	PBT	8P8C SHIELDED	1	JP010SX88X2XXXXJ-08
No	Name	Material	Specification	QTY	Remark

APPD.		P/N	STS
CHKD.		FILE	Performance - Tested to Category 6
DR.		TITLE	TL

REV.	DESCRIPTION	ENG.	Date	APPROVAL
------	-------------	------	------	----------

TUK Ltd		SCALE	UNIT	MM	SIZE	A4
		REV.	MM	REV.	A0	