

PCMX1U2FW

Dual FireWire™ and single USB Card



Dual FireWire™ and USB connectivity for Notebooks.

Is your existing Notebook or Desktop without the necessary next generation Ports to allow attachment to FireWire™ 1394a products such as the latest AV equipment, or have you run out of existing high speed USB2.0 Ports on your portable?

Introducing the new Dynamode PCMX1U2FW dual FireWire™ and single USB2.0 adapter designed for the class-leading ExpressCard™/34 slot. The replacement for the current PCMCIA standard, ExpressCard™ technology couples the higher bandwidth performance of PCI Express including much higher transfer rates of around 3Gbps needed for today's high-speed storage and data transfer devices such as external A/V and storage devices.

The best of both Worlds. FireWire™ and USB2.0

Integral dual FireWire™ 1394a compliant ports with up to 400Mbps transfer rates with low CPU overhead and integral USB2.0 for up to 480Mbps transfer rates. Built-in 5VDC output jack for high-current USB devices.

Full Windows® and MAC® OS X compliance, the new PCMX1U2FW is your ideal partner for the next generation in high-speed data transfer.



Dual FireWire™ Adapter

PCMX2FW



Dual SATA/11 Adapter

PCMX2S

Advanced features

ExpressCard™/34 type Adapter Card

Up to 3Gbps transfer rates ~ Plug n' Play

Dual FireWire™ 1394a Ports ~ up to 400Mbps

Single USB2.0 Port ~ up to 480Mbps

FireWire™ Hot Swappable on both Ports

5VDC output for higher current USB devices

Lower Power Consumption for Notebooks

Bundled FireWire™ and Power Output Cable

*Ideal for Windows® 2000/XP/XP 64-bit/Vista/7
MAC® OS X and Linux®*



Dynamode



Mac



© 2009 Dynamode UK
Details correct at going to Press. E&OE
All Trademarks Acknowledged.

Further product details available from www.dynamode.net