

Asus X54C-SX127V 39.6 cm (15.6") LED Notebook - Intel Pentium B960 2.20 GHz

Overview

Asus X54C-SX127V 39.6 cm (15.6") LED Notebook - Intel Pentium B960 2.20 GHz - 1366 x 768 WXGA Display - 8 GB RAM - 500 GB HDD - DVD-Writer - Intel Graphics Media Accelerator HD Graphics Card - Webcam - Genuine Windows 7 Home Premium - HDMI



Marketing Information

The ASUS X series notebook delivers perfect mobile performance, for both work and play. Exclusive dual-sided motherboard design places hot components on the underside and away from users. Combined with heatpipes and vents, palm rests and typing surfaces stay cooler than the body temperature so they're cool even during the longest computing sessions.



General Information

Manufacturer:	ASUS Computer International
Manufacturer Part Number:	X54C-SX127V
Manufacturer Website Address:	uk.asus.com
Brand Name:	Asus
Product Series:	X54
Product Model:	X54C-SX127V
Product Name:	X54C-SX127V Notebook
Product Type:	Notebook

Processor & Chipset

Processor Manufacturer:	Intel
Processor Type:	Pentium
Processor Model:	B960
Processor Speed:	2.20 GHz
Processor Core:	Dual-core (2 Core)
Cache:	2 MB
Direct Media Interface:	5 GT/s
64-bit Processing:	Yes
Hyper-Threading:	No

Memory

Standard Memory:	8 GB
------------------	------

Memory Technology:	DDR3 SDRAM
Memory Card Reader:	Yes
	<input checked="" type="checkbox"/> Secure Digital (SD) Card <input checked="" type="checkbox"/> Secure Digital High Capacity (SDHC) <input checked="" type="checkbox"/> MultiMediaCard (MMC) <input checked="" type="checkbox"/> Memory Stick
Memory Card Supported:	

Storage

Hard Drive Capacity:	500 GB
Hard Drive Interface:	Serial ATA
Optical Drive Type:	DVD-Writer
Optical Media Supported:	DVD±R/±RW
Dual-Layer Media Supported:	Yes

Display & Graphics

Screen Size:	39.6 cm (15.6")
Display Screen Type:	Active Matrix TFT Colour LCD
Aspect Ratio:	16:9
Screen Mode:	WXGA
Screen Resolution:	1366 x 768
Backlight Technology:	LED
Graphics Controller Manufacturer:	Intel
Graphics Controller Model:	Graphics Media Accelerator HD
Graphics Memory Technology:	DDR3 SDRAM
Graphics Memory Accessibility:	Shared

Network & Communication

Wi-Fi:	Yes
Wi-Fi Standard:	IEEE 802.11b/g/n
Ethernet Technology:	Gigabit Ethernet

Built-in Devices

Webcam:	Yes
---------	-----

Interfaces/Ports

HDMI:	Yes
Total Number of USB Ports:	3
Number of USB 2.0 Ports:	3
Network (RJ-45):	Yes

Software

Operating System: Genuine Windows 7 Home Premium
Operating System Architecture: 64-bit

Input Devices

Keyboard: Yes
Pointing Device Type: TouchPad
TouchPad Features: Multi-touch Gesture

Battery Information

Battery Chemistry: Lithium Ion (Li-Ion)

Physical Characteristics

Width: 378.0 mm
Depth: 253.0 mm
Weight (Approximate): 2.70 kg

Miscellaneous

Package Contents:

- X54C-SX127V Notebook
- Lithium Ion Battery
- AC Adapter

Green Compliant: Yes
Green Compliance Certificate/Authority: RoHS