

ABRR015 ROUND ROCKER SWITCH

SWITCHES

Specifications

ABRR015

Rating	6(2)A/250VAC T125/55 1E4 VDE 10A 125VAC UL C-UL		
Colour	Black body/Red illuminated		
Switch action	SP On-off		
Maximum contact resistance	30M Ω		
Minimum insulation resistance	500VDC 100M Ω		
Electrical life	10,000 cycles		
Operation force	300-600gf		
Operating temperature	-25°C~125°C		
Cut out	Z	Y	X
(diagram opposite)	0.75-1.25	20.8	20.2
	1.25-2.0	20.8	20.4
	2.0-3.0	20.8	20.6

Approval VDE, UL

Double pole versions available

Features

- ROHS compliant
- Housing material:
Nylon #66 UL 94V-2
- Rocker material:
PC UL 94HB
- Terminal material:
Copper alloy SN or AG plated
- Contact material:
AgNi (15) alloy

