



Technical Data Sheet for Solderpot Max

Technical specification	
Type	Solder Pots
Typical Operating Temperature	385°C
Solder Capacity	140g
Available Wattage	90W
Available Voltage	230V
Available Plug	BP
Frequency	50Hz / 60Hz
Base	Ceramic and Nylon
Crucible Diameter	39mm
Depth	126mm
Detachable Tray	Yes
Fixed Mains Cable	1.5 m; 3 Core Mains Cable
Part Number	CM82060 UK PLUG CM83060 EP PLUG
Solder suitability	Lead free solder
Fixing centre	4 Holes for Bench Fixing

- Suitable for tinning component leads, wires, tags etc
- Detachable tray surrounds crucible, retains excess dross when cleaning solder surface
- Pot seated on ceramic and nylon base 120mm x 120mm with 4 holes, fixing centres 100mm x 100mm, for bench fixing
- Heating element sets available separately