

Terminal markers
SCHT 5 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-2083

www.weidmueller.com



The **SchT 5 S** group tag carriers are clipped directly to the TS 32 DIN rail (G-rail) or the TS 35 DIN rail (top-hat rail). It is therefore possible to provide terminal strip labelling irrespective of the terminal and the type of terminal.

SchT 5 and **SchT 5 S** are fitted with ESO 5, STR 5 protective strips.

Inlay tags and protective strips can be found under "Accessories".

General ordering data

Order No.	1631930000
Type	SCHT 5 S
Version	Terminal markers, 44.5 x 9.5 mm, Polyamide 66
GTIN (EAN)	4008190206680

Terminal markers

SCHT 5 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-2083
 www.weidmueller.com

Technical data

Dimensions

Length	44.5 mm	Width	9.5 mm
--------	---------	-------	--------

Markings

Can be labelled with thermal transfer printers	No	Can be printed with plotter	No
Can be written with dot-matrix printer	No	Can be written with laser printer	No
Conductor O.D.	-	Flammability class UL 94	V-2
Material	Polyamide 66	Max. temperature, transient	80 °C
Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
Orientation of print	horizontal and vertical	Pitch in mm (P)	5 mm
Speed marking laser	No		

Classifications

ETIM 2.0	EC000761	ETIM 3.0	EC000761
UNSPSC	30-21-18-07	eClass 4.1	24-19-02-19
eClass 5.1	27-14-11-37	eClass 6.0	27-14-11-37
eClass 7.0	27-14-11-37		

Product information

Product description	The SCHT 5 & SCHT 5 S group marker carrier is clipped directly to the TS 32 DIN rail (G-rail) or the TS 35 DIN rail (top-hat rail). It is therefore possible to provide terminal strip labelling irrespective of the terminal and the type of terminal.
---------------------	---

Downloads

STEP	1631930000_20875_SCHT_5_S_STP.stp
------	---