


象牙紅座6u" P/N 3101745600 黑殼紅座6u" P/N 3101735600
 15u" P/N 3101745700 15u" P/N 3101735700
 30u" P/N 3101745800 30u" P/N 3101735800
 50u" P/N 3101745900 50u" P/N 3101735900



象牙紅座6u" P/N 3101715600
 15u" P/N 3101715700
 30u" P/N 3101715800
 50u" P/N 3101715900

MATERIALS:


PLASTIC HOUSING: ENGINEERING THERMOPLASTIC
 FLAMMABILITY RATING UL 94V-0.

CONTACTS: 0.35MM THICKNESS PHOSPHOR BRONZE

PLATING: GOLD PLATING OVER NICKEL IN CONTACT.

※凡標註△記號者，為品管檢驗之尺寸

Front Panel Jack Only Clearance Single Panel-Latch Clearance
 W/O Latch Feature Panel Thickness 0.062 inch

設計DR.	核准APPD.	容許公差 TOLERANCE	品名 ARTICLE MODULAR COUPLER JACK(8P8C)			
93.04.30	93.04.30	.XXX ±0.10 .XX ±0.25 .X ±0.38 X ±0.50 ANG ±3°	圖號 DWG NO. 3101-8821			
版本說明 REVISION NOTE						
MBS CONNECT			單位 UNIT mm	比例 SCALE 2/1	張數 SHEET 1/1	版本 REV. A