

Rectangular P.A. Horns - 100V Line



A range of rectangular shaped P.A. horn speakers manufactured from ivory coloured ABS. Fitted with a length of 3 core cable.

- Compact, rectangular design
- Line matching transformer
- Rotary transformer tapping selection switch
- Adjustable coated steel mounting brackets

	426-2920	426-2931
Power (RMS)	10W	15W
Power (Max.)	15W	30W
Frequency Response	315Hz to 12kHz	280Hz to 12kHz
Tappings	1/3/5/10W	1/3/5/10/15W
SPL @ 1W/1m	105dB	108dB
Dimensions (WxHxD)	175x125x182mm	224x160x230mm
Weight	1kg	1.5kg

249073

Description	Order Code	Price Each
15W	426-2920	
30W	426-2931	