20W Inspection & Machine Light





- Versatile low voltage 20W halogen light
 Four options of input voltage: 12V, 24V, 110V or 240V (with built in transformer)
 Robust and durable, suitable for a wide range of applications
 Stay-put & vibration resistant flexible arm 700mm
 Spot lamp 60mm base with a single jointed head
 On/off switch on base
 Easy to position and focus as required
 Magnetic base and protective head cover to IP54 available
 Supplied complete with lamp
 Suitable for manufacturing machines machine tools graphic design assembly in

- Suitable for manufacturing machines, machine tools, graphic design, assembly, inspection and precision mechanical work

Black Flex - 960mm / Spot - 260mm IP20 (IP54 with cover) Colour Total length IP rating

Mounting base Lamp housing

60 x 60mm

			000300
	Mftrs. List No.	Order Code	Price Each
Flex Lamps			
12V	14320	357-7120	
24V	14420	357-7132	
230V to 12V	14120	357-7107	
110V to 12V	14470	357-7119	
Spot Lamps			
12V	14360	472-5207	
24V	14360/2	472-5219	
Accessories			
Protective head cover	14080	357-7272	
Magnetic base	14000	357-7223	
Desk clamp	14020	474-356	
Transformer 400V to 12V	74400	472-5116	
Transformer 230V to 12V	74220	472-5104	
12V, 20W halogen bulb	15140A	357-7326	
24V, 20W halogen bulb	15141A	357-7338	