

Easy to use, reliable, industrial modems

Maestro 100 Evolution series is the perfect solution for demanding M2M applications. Compact and fully featured, the Maestro 100evo series can easily be integrated into industrial application from electricity meters to intrusion alarms or vending machines. Maestro 100evo modems are GPRS quadband and full type approved, making them immediately usable worldwide. Renowned for their outstanding reliability, Maestro 100evo modems are the perfect devices to integrate in each of your projects facing tough conditions or extended lifetime requirements.

100evo Series

100evo Crystal (Transparent bitpipe)

: GPRS, plastic casing

100evo Lite

: GPRS, Metal Casing,

+ Smart Pack Lite

+ 1 Digital Input

(local config.)

: GPRS, Metal Casing,

+ Smart Pack II

+ 1 Digital Input

100evo IP (remote config.)

(Advance temperature)

100evo Advance : GPRS, Metal Casing, IDS

+ Smart Pack II

+ 1 Digital Input

+ 1 Analog Input

+ Extended Temperature

Versatility

Maestro 100evo series provides different features regarding connectivity, intelligence or configuration software. You can thus get all the advantages of instant integration.











Technical information

empowering wireless

Maestro 100evo modems are available in metal or plastic casing.





Distributor's Contact

TECHNOLOGY				
GSM	Quadband			
GPRS	Class 10			
Voice/Data/Fax/SMS	/			
TCP/IP	Full TCP/IP Stack			
INTERFACES				
SIM Plug-in card reader	1.8/3 V.			
RS232 on 15 pin Sub-D connector	/			
Pin power supply connector	4 pin DC			
SMA antenna connector (50 ohm)	/			
POWER SUPPLY				
Input voltage	6 to 32V DC			
POWER CONSUMPTION				
GSM 850/900 (PCL 5)	203mA at 6V			
DCS 1800/PCS 1900 (PCL0)	140mA at 6V			
GPRS 850/900 CL10 (PCL5)	388mA at 6V			
GPRS 1800/1900 CL10 (PCL0)	232mA at 6V			
Idle consumption	45mA at 6V			
Idle consumption (RS232 not connected)	18mA at 6V			
Sleep Mode	4mA at 6V			
CERTIFICATIONS/COMPLIANCES				
CE, GCF, RoHS Certification				
VOICE, DATA AND SMS FEATURES				

FEATURES/PRODUCTS	M100evo Crystal	M100evo Lite	M100evo IP	M100evo Advanced
Input - Digital	N/A	1	1	1
Input - Analog	N/A			1
Download Over The Air	N/A		Optional	
Autorestore - timer reset			1	
OTHER FEATURES				
Operating status LED	/			
Casing	Plastic Metal			

Data circuit asynchronous, transparent and non-transparent up to 14,400 bit/s; Automatic fax group 3 (Class 1 and Class 2); MNP2, V.42bis; Text

> 300

and PDU SMS ; Point to point SMS (MT/MO) ; UCS2 Character Set Management

FUNCTIONAL FEATURES
AT command set (GSM 07.05, GSM

07.07 and Wavecom)

DIMENSIONS				
Size (mm)	88x60x26 90x72x23			
Weight (g)	70	70 100		
TEMPERATURE RANGE				
Operating / Storage		-30~+75 °C / -40~+85 °C	-30~+85 °C / -40~+85 °C	

OPTIONAL ACCESSORIES (ADDITIONAL ACCESSORIES ARE ALSO AVAILABLE UPON REQUEST)				
GSM antenna 900/1800 Mhz	1	1	1	1
GSM antenna 850/1900 Mhz	1	✓	1	1
RS232 cable interface	1	1	1	✓
Din Clin (metal casing only)	N/A	1	1	1

SMART PACK II FEATURES				
I/O Monitoring		✓	1	✓
GPRS and IP configuration		1	1	✓
Call Screening			1	✓
DynDNS	N/A	Smart Pack Lite	1	✓
Remote AT Command		Smart rack Lite	1	√
Ping		(Local Configuration)	1	✓
Status check and monitoring			1	1

Copyright Maestro Wireless Solutions Limited. We reserve the right at any time and without prior notice to modify or improve the modems and the services offered, the same applies to the accessories which could also be withdrawn.

Maestro Wireless Solutions Ltd 3603-9, 36/F 118 Connaught Road West Hong Kong Tel: (852) 2869 0688 Fax: (852) 2525 4701 contact@maestro-wireless.com www.maestro-wireless.com

