

HACKZALL™ M12™ Cordless LITHIUM-ION Recip Saw 2420-22

4.5 [Read 2 Reviews](#) [Write a Review](#)

At only 11" and 2.6 lbs, the HACKZALL® M12™ Cordless LITHIUM-ION Recip Saw features a compact and light weight design for superior control and versatility in tight spaces. A powerful motor delivers 0-3,000 strokes per minute and a 1/2" stroke length allows for fast cutting through a wide range of material such as drywall, wood, and PVC. The variable speed trigger allows for a controlled cut while a QUIK-LOK® blade clamp offers fast and easy blade changes.

Includes

- 2420-20 HACKZALL™ M12™ Cordless LITHIUM-ION Recip Saw
- (2) M12™ RED LITHIUM™ Batteries 48-11-2401
- 30-Minute Charger 48-59-2401
- (2) Hackzall™ Blades
- Carrying Case



FEATURES

- Only 11" and 2.6 lbs. for cutting in tight spaces
- M12™ RED LITHIUM™ Battery offers longer run-time and lighter weight
- Keyless QUIK-LOK™ Blade Clamp allows for quick and easy blade changes
- All-Metal Gear Case for added durability
- Variable Speed Trigger for increased user control
- Battery Fuel Gauge displays remaining run-time
- Accepts both HACKZALL™ and SAWZALL® style blades (See related products for listing of HACKZALL™ blades)
- Built-In LED Light illuminates work surface

SPECIFICATIONS

Voltage	12V
Speed	0-3000 SPM
Stroke Length	1/2"
Blade Clamp	QUIK-LOK® Universal 1/2" Tang
Trigger	Variable Speed
Battery	M12™ RED LITHIUM™
Length	11in
Tool Weight	2.6 lbs
Shipping Weight	7.6 lbs
No of Batteries Included	2

RESOURCES

	Manual	Parts Diagram
Service Info - 2420-22	B56A	B56A

RELATED ARTICLES

[Milwaukee Introduces New M12 HACKZALL™ Recip Saw](#)