

# LP

**0.5 – 1 – 2 – 5W  
Xenon Beacons**



# LT

**2 – 5W  
Xenon Beacons**



Fire



Industrial



Security

- Low current consumption
- Available in 6, 12, 24, 50, 110 and 230V versions
- Multivoltage option (10 - 100Vdc, 20 - 72Vac)
- Completely weatherproof to IP67 (when installed)
- High efficiency
- 360° visibility
- 12 months guarantee ~ 5 years in intruder alarm systems (LP)

### materials:

Polycarbonate Lens on 110V, 230V and Multivoltage.  
Others high impact acrylic.

High impact polystyrene base.

### accessories:

A range of accessories is available for both beacons.  
Please see separate Accessories Leaflet.


### lens colours:

Clear, Amber, Red, Blue or Green.

# LP and LT Xenon Beacons


## technical specification - LP series:

MODEL	VOLTAGE	VOLTAGE RANGE	POWER OUTPUT	CURRENT CONSUMPTION (mA)					FLASH RATE
				@6V	@12V	@24V	@50V	@100V	
LP1X12/0.5	12	10 - 15 Vdc	0.5W	-	50	-	-	-	60/MIN
LP1XMV/0.5	MULTI	10 - 100 Vdc 20 - 72 Vac	0.5W	-	60	37	30	20	60/MIN
LP1X06/1	6	4.7 - 7.5 Vdc	1W	240	-	-	-	-	60/MIN
LP1X12/1	12	10 - 15 Vdc	1W	-	115	-	-	-	60/MIN
LP1X24/1	24	20 - 30 Vdc	1W	-	-	55	-	-	60/MIN
LP1XMV/1	MULTI	10 - 100 Vdc 20 - 72 Vac	1W	-	112	63	50	29	60/MIN
LP1X12/2	12	10-15 Vdc	2W	-	220	-	-	-	60/MIN
LP1X24/2	24	20 - 30 Vdc	2W	-	-	110	-	-	60/MIN
LP1X24/2ac	24ac	20 - 30 Vac	2W	-	-	100	-	-	60/MIN
LP1X50/2	50	40 - 55 Vdc	2W	-	-	-	55	-	60/MIN
LP1X110/2ac	110ac	90 - 125 Vac	2W	-	-	-	-	-	60/MIN
LP1X230/2ac	230ac	207 - 253 Vac	2W	-	-	-	-	-	60/MIN
LP4XMV/2	MULTI	10 - 100 Vdc 20 - 72 Vac	2W	-	130	95	83	37	75/MIN
LP3X12/5 Sync	12	10 - 15 Vdc	5W	-	360	-	-	-	90/MIN
LP3X24/5 Sync	24	20 - 30 Vdc	5W	-	-	160	-	-	90/MIN
LP4XMV/5	MULTI	10 - 100 Vdc 20 - 72 Vac	5W	-	250	200	112	60	75/MIN



## technical specification - LT series:

MODEL	VOLTAGE	VOLTAGE RANGE	POWER OUTPUT	CURRENT CONSUMPTION (mA)					FLASH RATE
				@6V	@12V	@24V	@50V	@100V	
LT4XMV/2	MULTI	10 - 100 Vdc 20 - 72 Vac	2W	-	130	95	83	37	75/MIN
LT2X06/5	6	4 - 7 Vdc	5W	1000	-	-	-	-	120/MIN
LT3X12/5	12	10 - 15 Vdc	5W	-	360	-	-	-	90/MIN
LT3X24/5	24	20 - 30 Vdc	5W	-	-	160	-	-	90/MIN
LT2X50/5	50	40 - 60 Vdc	5W	-	-	-	100	-	120/MIN
LT3X110/5ac	110ac	90 - 125 Vac	5W	-	-	-	-	-	90/MIN
LT3X230/5ac	230ac	207 - 253 Vdc	5W	-	-	-	-	-	90/MIN
LT4XMV/5	MULTI	10 - 100 Vdc 20 - 72 Vac	5W	-	255	190	112	70	75/MIN



CE

High voltage transient and polarity reversal protection fitted.  
CE - Complies with EMC Directive 89/336/EEC and Low Voltage Directive 73/23/EEC, where appropriate.

Primrose Hill, Kings Langley, Herts WD4 8ST, England.

Tel: (U.K.) 01923 269522  
(Int.) +44 1923 269522

Fax: (U.K.) 01923 260167  
(Int.) +44 1923 260167

E-mail: sales@deltadesign.co.uk  
Web: http://www.deltadesign.co.uk

