

Di-Polar Ceiling Speaker



A ceiling speaker that provides both left and right stereo channels from a single point, whilst maintaining complete channel isolation. The speaker has 2x \varnothing 12.7mm (1/2") mylar dome tweeters, combined with a dual voice coil, 165mm (6 1/2") polypropylene woofer.

- Full, rich frequency response
- White ABS frame
- White, perforated steel grilles
- Mounting tags provide quick and easy mounting
- 6.35mm Push-On/Solder terminals

Power Rating 25W RMS/60W peak per channel
Impedance 8 Ω
Frequency Response 70Hz to 20kHz
Sensitivity 88dB

Overall Frame \varnothing 230mm (9")
Cutout \varnothing 190 (7 1/2")
Mounting Depth 83mm

383379.260846

Price Each

Order Code
867-0820