




SLIDER POTENTIOMETER KNOBS CS SERIES

Eight different designs are produced. 3 types have option of 4mm. 6/8mm shaft fitting. All knobs have matt non reflective finish to match our K9-K12 series and C18. Standard colour - Black. Electrically conductive models available.



L 23mm, W 11mm, H 11mm

CS1 - for 6/8mm shaft
CS1A - for 4mm shaft
CS1B - fro 4mm shaft



L 27mm, W 16mm, H 7mm

CS9 - for 6/8mm shaft
CS9A - for 4mm shaft



L 17mm, W 10mm, H 8mm

CS8 - for 6/8mm shaft
smaller version of CS1



L 27mm, W 13mm, H 8mm

CS10 - for 6/8mm shaft
Narrower version of CS9



L 20mm, W 14mm, H 13mm

CS2 - for 6/8mm shaft
CS2A - for 4mm shaft
CS2B - for 4mm shaft



Diameter 8mm, Height 8mm
CS-11

Designed to fit square shaft
of push button switches and
4mm or 6mm slider shafts.



L 12mm, W 9mm, H 9mm

CS7A - for 4mm shaft

CS7C - for 4mm shaft




L 12mm, W 12mm, H 10mm
CS-12


Designed to fit 3.3mm shaft
of push button switches.

SHAFT DETAILS (TYPICAL)

4mm TYPE 'A' (std)




4mm TYPE 'B' (special)




TYPE B subject to viable qty.

8mm TYPE



6mm TYPE



Note: Other colours or shaft fittings available subject to economical quantity.

Drawings available on request. Contact sales@cliffuk.co.uk