

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [88941-0700](#)
Status: **Active**
Overview: [KK® Interconnection System](#)
Description: 2.50mm Pitch Dual-ended KK® Cat Ear Crimp Wire Harness, 300mm, AWG 24

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	88900
Comments	Cable-end Crimp Terminals 8500031
Connector to Connector	KK® Cat Ear Crimp Terminals
Overview	KK® Interconnection System
Product Name	KK®

Physical

Cable Length	0.30m
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Plating Mating	Tin
Pitch - Mating Interface	2.50mm
Plating min - Mating	1.016µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Waterproof / Dustproof	No
Wire Size AWG	24
Wire/Cable Type	Round

Electrical

Shielded	No
----------	----

Material Info

UPC	883906556709
-----	--------------

Reference - Drawing Numbers

Sales Drawing	SD-88941-0700
---------------	---------------

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[88900Series](#)

Mates With

[8500031](#) Crimp Terminals