

Indoor Break Glass Call Points



- Indoor surface mounting call points available as 470Ω or 680Ω versions
- Unique 'Plug & Play' installation concept
- Anti-tamper facility
- Enhanced aesthetics
- Fully approved to the latest standards, including EN54-11 and LPCB 166b/39 & 166b/40
- Backward compatibility
- Additional transparent hinged covers available for extra protection, ideal for schools etc
- Operating Temperature: -40 to +55°C
- Voltage: 24V DC
- Dimensions (WxHxD): 89 x 93 x 58.5mm

416661.416656

Description	Order Code	Price Each
Call Point 470Ω	100-4630	
Call Point 680Ω	100-4631	
Accessories		
Hinged Cover	100-4632	
Hinged Cover Seals (Pk5)	100-4634	
Spare Glass (Pk10)	890-1970	
Spare Keys (Pk10)	100-4635	