

# HL Stick – The new expert for fine working

## TECHNICAL DATA

Product code:	004019
Dimensions (h x w x d):	780 x 760 x 2350 mm
Voltage:	230 v 50 Hz
Output:	350 W
Temperature:	400 °C, 500 °C with reduction nozzle
Air Flow:	100 l/min
Switches:	1 (On/Off)
Specials:	Incl. LED / Stable hanging
Length Power Cord:	2.20 m
Weight:	572 g
Motor:	Brush motor
Heating element:	Ceramic
Accessories included:	7mm reduction nozzle, reduction nozzle with protection reflector, 10mm and 40mm reflector nozzles

Available April 2012



**Working punctual and precise with hot air!**

**This small ergonomically shaped hot air tool enables work in confined places as well**

Steinel (UK) Limited

25 Manasty Road, Axis Park, Orton Southgate, Peterborough, PE2 6UP

Tel: 01733 366700 ~ Fax: 01733 366701 ~ Email: [steinel@steinel.co.uk](mailto:steinel@steinel.co.uk) ~ Website: [www.steinel.co.uk](http://www.steinel.co.uk)