
Item no.: 264-716
Product description: 2-CONDUCTOR MINIATURE THROUGH TERMINAL BLOCK



Produkt kann von Bild abweichen / product may differ

Packing unit 100 pieces

RoHS compliant

Product group	9 (Std Chassis Mt Blocks)
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP [®] CONNECTION
Measured voltage EN	800 V
Measured shock voltage	8 kV
Pollution degree	3
Current intensity EN	24 A
Weight	3.96 g
Color	orange
Wiring type	Front-entry
No. of connection Points	2
No. of potentials	1
Height	24.5 mm
Height	0.96 in
Width	6 mm
Width	0.236 in
Depth	38 mm
Depth	1.5 in

Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
264-716	ABS	04-HG476174/1-PDA	800	24	2,5
264-716	BV	07436/C0			0,08-2,5
264-716	CSA	18677-23	600	20	26-12
264-716	DNV	E-9215	800	24	2,5
264-716	GL	17295-00HH	800	24	4
264-716	KR	HMB05880-EL002	800	24	
264-716	LR	92/20242(E5)	800	24	2,5
264-716	PRS	TE/1718/880590/08	800		2,5
264-716	RMR	11130002	800	24	2,5
264-716	UR	E45172	300	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected