


REV	MODIFICATION	DATE	DRAW
I	EN-10-1015	99/10/20	SAN
J	EN-10-1121	99/11/18	SAN
K	EN-11-0508	100/05/06	Stacy



HOUSING: LCP UL 94V-0
 CONTACT: SELECTIVE GOLD FLASH
 SPECIFICATIONS
 VOLTAGE CURRENT RATING: 1A, 50V AC
 INSULATION RESISTANCE: 1000Mohm Min
 CONTACT WITHSTANDING VOLTAGE:
 AC 500V FOR 1 MINUTE
 TEMPERATURE RATING: -40°C ~ +85°C

ORDER INFORMATION:
 SIMMP-00 X 01B2 X X - G
 COMPLY TO RoHS
 6: 6PIN (REMOVE C4&C8)
 8: 8PIN
 0: WITHOUT POST
 1: WITH POST
 0: TUBE
 1: T&R (700PCS/R)

PCB LAYOUT RECOMMENDED



DIMENSION IN mm [Inch]		PROD. SPEC.	C KINGFONT KINGFONT PRECISION INDUSTRIAL CO., LTD.	
TOLERANCE UNLESS OTHERWISE SPECIFIED		PKG. SPEC.	TITLE SIM CARD ACCEPTOR CUSTOMER DRAWING	
.X±0.25	X.*±	APPROVE Garry	FILE NO.	DWG NO. SIMMP-00X01B2XX-G
.XX±0.15	.X.*±	CHECK Tony	SIZE A4	PROJ. SHEET 1 / 1
.XXX±0.10	.XX.*±	DRAW Sjo	SCALE 2.5:1	REV K