


# GSR Mx2Drive Professional

Cordless screwdriver



## *Advantages: GSR Mx2Drive Professional*

### *Maximum power in trouser-pocket size*

- Maximum power: innovative 2-speed gearbox allows for the gear to be changed without interruption by the on/off switch, and provides a powerful 10 Nm
- Fast and precise due to optimum gear ratio: fast driving in 2nd gear (0 – 580 rpm) – precise and flush driving in 1st gear (150 rpm)
- Extremely compact: very short head length (only 158 mm) and low weight (only 0.5 kg) – fits in any trouser pocket
- Lockable 1/4" universal bit holder locks all conventional drill bits and screwdriver bits
- Multi charger: charges both 3.6 volt and 10.8 volt batteries within one hour
- Unique Bosch Premium lithium-ion technology for longer lifetime and unbeatable battery runtime
- Bosch Electronic Cell Protection (ECP): protects the battery against overload, overheating and deep discharge
- Motor brake for precise work when driving rows of screws
- Integrated LED light for illuminating the work area, even in dark places
- No memory effect: the battery can be charged regardless of the charging state at any time, without damaging the cells

### *Technical data: GSR Mx2Drive Professional*

Torque, max. (hard screwdriving applications)	10 Nm
Torque, max. (soft screwdriving applications)	5 Nm
No-load speed (1st gear / 2nd gear)	150 / 0 – 580 rpm
Battery voltage	3,6 V

Torque, max. (hard screwdriving applications)	10 Nm
Weight incl. battery	0,5 kg
<b>Drilling diameter</b>	
Max. drilling diameter in wood	5 mm
<b>Screw diameter</b>	
Max. screw diameter	5 mm

### *Functions*

- Forward/reverse operation
- Electronic
- Auto-Lock
- Softgrip
- Light

### *Noise/vibration information*

Measured values determined according to EN 60745.  
Total vibration values (vector sum of three directions)

<b>Screwdriving</b>	
Vibration emission value ah	2.5 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>