

## GWB 10.8v Angle Drill Driver



Bosch GWB 10.8 VLI li-ion Cordless Angle Drill Driver complete with 2 batteries, charger and L-boxx

The GWB10.8VLI from Bosch offers both angled and in-line drilling and driving making it an extremely versatile and compact tool

### ***FEATURES:***

---

- Drilling and driving at a straight 0 degree angle as well as at angles of 22.5, 45, 67.5 and 90 degrees
- Very compact due to the short length and the small adjustable chuck
- Great performance from the motor providing 1300 rpm, great for small screwdriving and drilling applications
- ECP (Electronic Cell Protection) provides long runtime and long life of batteries
- The L-Boxx storage system is durable, robust and can be integrated into vehicles

### ***PRODUCT SPECIFICATION***

---

- Battery voltage / capacity: 10.8 V / 1.3 Ah
- Machine weight with battery: 1.2 kg
- No-load speed: 0 - 1300 rpm
- Max. screw diameter: 6 mm

- Max drilling dia. for steel: 10 mm
- Max drilling dia. for wood: 35 mm
- Drilling positions: 5
- Total Shipping Weight: 4kg

### ***APPLICATIONS:***

---

- Working overhead in tight areas
- Drilling holes in wood and metal
- Fixation on metal construction frames
- Driving midsize screws in soft wood

### ***COMES WITH:***

---

- 2 x 1.3ah li-ion batteries
- Charger
- L-Boxx