

6.01405.50 STA 18 LTX 140

18 Volt Cordless Jig Saw STA 18 LTX 140

- Extremely powerful jig saw with VTC electronics for fast cuts into softwood of up to 140 mm
- High sawing performance: in excess of 40 metres in chipboard (19 mm) with only one battery pack charge
- Extremely easy to handle: slimline handle with rubberised surfaces
- Precise and material-matched sawing thanks to the variable stroke rate, pendulum stroke and low-lying saw blade guidance with spring support
- Metabo "Quick" no-tool saw blade change function with automatic rejection
- Convenient start automatic: automatic stroke acceleration when starting to saw
- Simple bevel cuts thanks to no-tool adjustable footplate with rest points
- Switchable shaving blower function ensures free view of cutting line
- Integrated LED work light for optimum illumination of the cutting line
- Vario-Tacho-Constamatic (VTC) full wave electronics: maximum sawing progress thanks to constant stroke rate even under load
- Restart protection: Prevents unintentionally starting the machine.
- Robust gear and motor design and durable die cast aluminium gear housing
- Sawing with a system: circle-cutting and parallel guide, guide rail adapter as well as various protective plates expand the spectrum of applications
- World innovation! With a 4.0 Ah battery pack for 33% longer operating time per charge.
- Patented AIR COOLED technology for speedy charging and long service life
- Robust battery packs with capacity display for checking the charge status
- Metabo Ultra M technology: Intelligent battery management for long-lasting battery packs with a 3 year guarantee

Vergleichbare Gerätekenwerte

Type of battery pack	Li-ion
Battery pack voltage	18 V
Maximum thickness of material in	
- Wood	140 mm
- Non-ferrous metals	35 mm
- Steel sheet	10 mm
Swivel range from / to:	+ 45 °/- 45 °
Pendulum stroke levels	4
Strokes in idle	1.000 - 3.000 /min
Weight (including battery pack)	2,9 kg

Scope of delivery

Extraction nozzle, Protective glass, plastic guard plate, 2 Li-Power Extreme battery packs (18 V/4.0 Ah), "AIR COOLED" quick charger ASC 30, Plastic carry case