



PW-600

Power Adapter 5V 1A Terminal

Description

This power supply is for ES-357. Features: INPUT: 100-240V ~ 0.4A 47-63Hz, OUTPUT: 5V DC 1.2A, VW-1 Rated, UL Approved, CE Approved, RoHS Compliant. Plug fittings cover 189 countries world wide.

Power Supply Input

100-240V ~ 0.4A 47-63Hz

Power Supply Output

5V DC 1.2A

Power Supply Power Plug

EU (type C)

Power Supply Input

100-240V ~ 0.4A 47-63Hz

Power Supply Output

5V DC 1.2A

Power Supply Length

1.530 mm

Power Supply Power Plug

EU (type C)

Power Supply Temperature Operating

0? to 40?

Power Supply Temperature Storage

-10? to 70?

Power Consumption

awaiting

Product Weight

0.176 kg, 0.39 pounds

Product Dimensions

110(l) x 60(w) x 70(h) mm, 4.33(l) x 2.36(w) x 2.76(h) inches

Packaged Weight

0.281 kg, 0.62 pounds

Packaged Dimensions

150(l) x 140(w) x 40(h) mm, 5.91(l) x 5.51(w) x 1.57(h) inches

GTIN-12

837324002812