



Drawings not to scale
All dimensions in mm

This non-mercury sensor has been specifically designed for the detection of movement and vibration. The sensor is non position sensitive offering a similar level of sensitivity whatever its position and has been designed for use with analogue or digital circuitry. The sensor reacts when disturbed by giving a fleeting change of state (ie n/o to n/c or vice versa). The time taken to settle depends on the amount of energy absorbed by the device, the settled state will be random unless mounting attitude is chosen for a n/c output.

The low contact resistance of this device makes it ideal for incorporating into new or existing designs.

SPECIFICATION

SWITCHING VOLTAGE	Max. Vac	24
SWITCHING CURRENT	Max. A	0.025
SWITCHING CAPACITY	Max. VA	5
OPERATING ANGLE	Max. °Deg	N/A
CONTACT RESISTANCE	Max. Ω	5
OPERATING TEMPERATURE	Deg. °C	-37° +100°
STORAGE TEMPERATURE	Deg. °C	-40° +125°
CASE MATERIAL		Steel - Gold plated
CABLE/TERMINATION		Pin
FEATURES		Non-mercury contacts Omni-Directional

NOTE: When cutting switch leads it is important that the glass seal is not damaged. The cutting point should be no closer than 3mm to the glass to metal seal and the lead should be supported between the cutting point and the glass to metal seal.

Patent App. 98 09677.9

MOTION SWITCHES - Metal

PART NUMBER
MS 24

Rev. No.	Revision Note	Date	Signature
C	Web Site	1-5-99	RG



BS5750/ISO 9000
Reg. No. FM 21080

As part of the company policy of continued product improvement, specifications may change without notice. Our sales office will be pleased to help you with the latest information on this product range and details of our full design and manufacturing service. All products are supplied to our standard conditions of sale otherwise agreed in writing.