



[Back](#)

**Selected Cable: 17038A**

End View	Plug	Cord	Connector	End View
1-15P	S-289-SNT	SPT-2	913	C7

<b>Part Number</b>	17038A
<b>Category</b>	appliance and electronic
<b>Subcategory</b>	laptop
<b>Jacket Color</b>	Gray or Black
<b>Length Feet</b>	6'7
<b>Length Meters</b>	2
<b>Temperature Rating</b>	60 C°C
<b>Packaging Units Per Carton</b>	H-25,S-25
<b>AWG Stranding</b>	18 (41x34)
<b>Nominal OD Inch</b>	.144x280
<b>Nominal OD millimeter</b>	3.66x7.11
<b>Rating</b>	312.5 Watts 2.5A-125V
<b>Notes</b>	See 17036 for C5 connector version.

**Cord View**



**Approvals**



Qty:

**Back**

Volex Power Cord Products Division, 5350 Lakeview Parkway S. Drive #D Indianapolis, IN 46268  
800-246-CORD. [info@volexpowercords.com](mailto:info@volexpowercords.com)

Proposition 65 warning for California residents: This product contains chemicals, including lead, known to the State of California to cause (cancer, and) birth defects or other reproductive harm. Wash hands after handling.

