

Soldering Irons, SP Series

Fine Duty Irons, 15 Watts

- For fine duty work such as in home electronics, light duty electrical repairs and hobby work.
- Fitted with straight tip, nickel-plated 2,0 mm (type S5).
- ON / OFF indicator light



Type / Code No.	Watts	Volts	Hz	Weight g	Shelf Pack
SP15LEU (VDE)	15	230	50	338	6
SP15LUK (GB)	15	230	50	350	6
SP15LCH (CH)	15	230	50	338	6
SP15ISR (ISR)	15	230	50	348	6
SP15LZA (ZA)	15	230	50	348	6
SP15LDK (DK)	15	230	50	338	6

General Duty Irons, 25 Watts

- All-purpose iron for general electrical repairs in the home and hobby workshop.
- Fitted with straight tip nickel-plated 0,8 mm (type MT1).
- ON / OFF indicator light



Type / Code No.	Watts	Volts	Hz	Weight g	Shelf Pack
SP25LEU (VDE)	25	230	50	369	6
SP25LUK (GB)	25	230	50	380	6
SP25LCH (CH)	25	230	50	369	6
SP25ISR (ISR)	25	230	50	380	6
SP25LZA (ZA)	25	230	50	380	6
SP25LDK (DK)	25	230	50	369	6

Medium Duty Irons, 40 Watts

- Medium duty iron for most general soldering repairs where a little more power is required.
- Fitted with straight tip, nickel-plated 6,3 mm (type MT10).
- ON / OFF indicator light



Type / Code No.	Watts	Volts	Hz	Weight g	Shelf Pack
SP40LEU (VDE)	40	230	50	402	6
SP40LUK (GB)	40	230	50	412	6
SP40LCH (CH)	40	230	50	402	6
SP40ISR (ISR)	40	230	50	412	6
SP40LZA (ZA)	40	230	50	412	6
SP40LDK (DK)	40	230	50	402	6