



ROEBUCK TOGGLE CLAMP MG1B

Base mounted

Solid bar with spindle retainer supplied loose for welding in desired position

Supplied with set screw and nuts

Manufactured from zinc plated and passivated steel

| | |
|--------------------------|--------------|
| Clamping pressure | 270 kg |
| Dimension A | 275 mm |
| Dimension B | 79 mm |
| Dimension C | 64 mm |
| Dimension D | 126 mm |
| Dimension E | 60 mm |
| Dimension F | 44 mm |
| Dimension G | 67 mm |
| Dimension H | 10.5 mm |
| Dimension I | M12 x 100 mm |
| Dimension, A | 275 mm |
| Dimension, B | 79 mm |
| Dimension, C | 64 mm |
| Dimension, D | 126 mm |

| | |
|-------------------------|--------------|
| Dimension, E | 60 mm |
| Dimension, F | 44 mm |
| Dimension, G | 67 mm |
| Dimension, H | M12 X 100 mm |
| Holding pressure | 545 kg |
| RoHS Compliant | NA |
| Weight | 1.80 kg |