

Specialty Tools & Instruments



SITE NAVIGATION » Find a Distributor » Media Resources » Press Releases » Product Manuals



SAM990DW - DIGITAL PSYCHROMETER WITH DEW POINT AND WET BULB Item Id: SAM990DW Product Overview DIGITAL PSYCHROMETER WITH TEMPERATURE, HUMIDITY, DEW POINT & WET BULB (BLISTER PACK)

Wide applications in monitoring environmental conditions.

Features & Benefits :

- Displays wet bulb, dew point, humidity and temperature
 No twirling or charts necessary
 Large digital display
 Dew point measurement
 Wet and dry bulb temperature
 Min/Max memory
 °F or °C readings
 Data hold
 Auto power off
 Low battery indication

Specifications :

- Temperature Measurement Range:-4° to 122°F (-20° to 50°C
 Temperature Measurement Accuracy:±1.8°F (±1°C)
 Relative Humidity Measurement Range:10 to 90%RH
 Measurement Accuracy:±3% of reading
 Dew Point Measurement Accuracy:±1.2°F (±0.6°C)
 Response Time: 60 seconds (approx.)
 Dimensions: 6.7 x 1.85 x 0.5 in.
 Power Source: 2 AAA batteries (included)

Includes :

· Protective cap with pocket clip

#N/A