

## x16 (09)

### 2.1 high fidelity subwoofer speaker system for multimedia and music entertainment

#### Features:

- Powerful 2.1 high fidelity subwoofer speaker system for full range acoustics
- Clear high frequency satellites can be place on desk, or wall mounted (Stand options available)
- Deep powerful bass and excellent sound quality with wooden cabinets
- Front panel and wireless remote control for easy access and control
- Bass reflex tunnel for depth and vocal production



#### Specifications:

##### Amplifier

- Output power: 68 Watt RMS
- Power distribution: 14 Watt x 2 + 40 Watt
- Harmonic distortion: < 0.3% 1W 1kHz
- Frequency response: 30Hz - 20kHz
- Signal/Noise ratio: > 75dB
- Separation: > 48dB
- Input sensitivity: 310mV
- Nominal impedance: 4 ohm

##### Speakers

- Tweeter driver type: 2.5" x 2
- Tweeter rated power: 15 Watt x 2
- Bass driver type: 6.5"
- Bass rated power: 60 Watt
- Frequency range: 30Hz - 20kHz

##### Interfaces

- Output: 2RCA
- Input: 3.5mm stereo, 2RCA

##### Power

- Power supply: AC 220V - 240V, 50Hz 450mA

##### Package contents

- x16 subwoofer
- x16 satellites x 2
- Wireless remote control
- Wireless remote control
- User manual

##### Dimension

- Subwoofer dimension: 220 x 310 x 285mm
- Satellites dimension: 100 x 203 x 124mm
- Product net weight: 8.8kg
- Giftbox dimension: 360 x 279 x 461kg
- Giftbox gross weight: 10.1kg
- Export carton dimension: 574 x 372 x 480mm
- Export carton gross weight: 21.9kg

**Warranty Notice:** \*1 Year Warranty

**Microlab Technology Company Limited**

EAN: 694519885048 5

Ver: 1.0



Product image, Terms and Specifications are subject to changes without further notice

© 2010 Microlab Technology Co., Ltd