

Compact and convenient push sweeper for indoor and outdoor use

Standard accessories:

- Manual sweep drive
- Fold-down push handle
- Dustpan principle
- Outdoor applications
- Indoor applications

Order no.: 1.517-151.0

**Technical data**

Drive	manual
Drive – power	-
Max. area performance (m ² /h)	2800
Working width (mm)	480
Working width with 1 side brush (mm)	700
Working width with 2 side brushes (mm)	-
Container capacity gross/net (l)	42/20
Filter area (m ²)	-
Weight (kg)	20
Dimensions (L x W x H) (mm)	1300x810x1040
Weight incl. packaging (kg)	25
Dimensions packaging (L x W x H) (mm)	795x400x935
Charging time rechargeable battery	-
Battery running time	-

Details

Description

The KM 70/15 C is an entry level high-value push sweeper with professional build-quality and a range of professional features. Sweeping 7 x faster than a conventional broom, the 70/15 also controls dust better and guarantees consistent, thorough results. Featuring an adjustable side brush for cleaning right up to kerb edges. Ideal for cleaning paths, halls and warehouses quickly and efficiently.

Features & Benefits

Main roller brush drive

The main roller brush is driven by both wheels – for excellent cleaning results even in tight corners.

Adjustable push handle

Excellent ergonomics due to triple adjustment option.

Foldable for space-saving parking.

Large dirt container

Ergonomic container grip for easy handling and emptying.

Dust filter

Dust filter cleans the exhaust air and prevents dust development while sweeping.

Accessories

Main roller brush, soft/ moisture-proof

Main roller brush, soft/ moisture-proof

Sweeps fine dust on all surfaces indoors and outdoors

Order no. 6.903-995.0



Other mounting kits

Litter Picker

Litter picker for collecting litter manually

Order no. 2.640-908.0




Standard main roller brushes

Standard main roller brush

Moisture-proof universal bristles, longlife, suitable for all surfaces

Order no. 6.907-041.0



Standard side brushes

Standard side brush

Standard side brush with moisture-proof universal bristles for normal soiling on all surfaces. Extremely durable.

Order no. 6.966-005.0

