

Control station selection



Point-of-purchase packaged pilot devices

Emergency stop operators

Features	Replaces Allen-Bradley Catalog Numbers	Square D Catalog Numbers	Catalog Number
Red non-illuminated push-pull button Includes 1NO-1NC contacts Maintained push-pull button Includes "STOP" and "EMERGENCY STOP" legend plates Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight Rated for 600 Vac/Vdc maximum For panels up to 1/4-inch thick, including the legend plate	800TFR01 800TFR02 800TFR03	90001SKR9RH5 90001SKR9RH6 90001SKR9RH13	10250T5B62-1-POP
Red mushroom pushbutton Includes 1NO-1NC contacts Includes "STOP" and "EMERGENCY STOP" legend plates Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight Rated for 600 Vac/Vdc maximum For panels up to 1/4-inch thick, including the legend plate	800TDFD1 800TDFD2 800TDF0A	90001KR4RH5 90001KR4RH6 90001KR4RH13 90001KR2RH5 90001KR2RH6 90001KR2RH13	10250T32R-POP
Red jambo mushroom pushbutton Includes red-colored button engraved "EMERG. STOP" Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight Rated for 600 Vac/Vdc maximum For panels up to 1/4-inch thick	800TDF01 800TDF02 800TDF0A	90001KR5RH5 90001KR5RH6 90001KR5RH13 90001KR2RH5 90001KR2RH6 90001KR2RH13	10250T33-POP

Momentary pushbuttons

Features	Replaces Allen-Bradley Catalog Numbers	Square D Catalog Numbers	Catalog Number
Black flush pushbutton Includes 1NO-1NC contacts Includes "START" and "JOG" legend plates Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight Rated for 600 Vac/Vdc maximum For panels up to 1/4-inch thick, including the legend plate	800TAD1 800TAD2 800TAD3	90001KR1RH5 90001KR1RH6 90001KR1RH13	10250T30B-POP
Red extended pushbutton Includes 1NO-1NC contacts Includes "STOP" legend plate Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight Rated for 600 Vac/Vdc maximum For panels up to 1/4-inch thick, including the legend plate	800TBD1 800TBD2 800TBD3	90001KR3RH5 90001KR3RH6 90001KR3RH13	10250T31R-POP

Indicating lights

Features	Replaces Allen-Bradley Catalog Numbers	Square D Catalog Numbers	Catalog Number
Red indicating light Includes one "RUN" and one "JOG" legend plate Includes green and amber lenses Full voltage 24 Vac/Vdc Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight For panels up to 1/4-inch thick, including the legend plate	800TQ24R 800TQ24A 800TQ24B	90001KPS3R31 90001KPS3R31 90001KPS3A31 90001KPS3R32 90001KPS3A32	10250T26NCIN-POP
Red indicating light Includes one "RUN" and one "JOG" legend plate Includes green and amber lenses Transformer 120 Vac 50/60 Hz Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight For panels up to 1/4-inch thick, including the legend plate	800TPI6R 800TPI6G 800TPI6A	90001KPI3R31 90001KPI3R32 90001KPI3A31 90001KPI3A32 90001KPI3R33 90001KPI3A33	10250T34R-POP

Illuminated pushbuttons

Features	Replaces Allen-Bradley Catalog Numbers	Square D Catalog Numbers	Catalog Number
Red illuminating pushbutton Includes 1NO-1NC contacts Includes green and amber lenses Includes one "POWER ON" legend plate Full voltage 24 Vac/Vdc Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight For panels up to 1/4-inch thick, including the legend plate	800TQB24R 800TQB24G 800TQB24A	90001SKL35AH5 90001SKL35AH6 90001SKL35AH13 90001SKL35RH5 90001SKL35RH6 90001SKL35RH13	10250T476C21-POP
Red illuminating pushbutton Includes 1NO-1NC contacts Includes green and amber lenses Includes "POWER ON" legend plate Transformer 120 Vac 50/60 Hz Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight For panels up to 1/4-inch thick, including the legend plate	800TPI6RD1 800TPI6GD1 800TPI6AD1 800TPI6RD2 800TPI6GD2 800TPI6AD2	90001SKL36RH5 90001SKL36RH6 90001SKL36RH13 90001SKL36RH5 90001SKL36RH6 90001SKL36RH13 90001SKL36AH5 90001SKL36AH6 90001SKL36AH13	10250T411C21-POP

Selector switches

Features	Replaces Allen-Bradley Catalog Numbers	Square D Catalog Numbers	Catalog Number
Black knob, two-position selector switch Knob selector switch Assembled with 1NO-1NC contact block Includes "ON/OFF", "HAND/AUTO" and "RUN/JOG" legend plates Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight Rated for 600 Vac/Vdc maximum For panels up to 1/4-inch thick, including the legend plate	800TJ2A 800TJ2D 800TJ2Z	90001KS11RH5 90001KS11RH6 90001KS11RH13	10250T20KB-POP
Black knob, three-position selector switch Knob selector switch Assembled with 1NO-1NC contact block Includes "HAND/OFF/AUTO" legend plate Rated for NEMA Types 4/4X/12/13 (indoor and outdoor) Heavy-duty oiltight Rated for 600 Vac/Vdc maximum For panels up to 1/4-inch thick, including the legend plate	800TJ2A 800TJ2D 800TJ2Z	90001KS43RH5 90001KS43RH6 90001KS43RH13	10250T22KB-POP



Die cast, polyester and stainless steel enclosures for 30 mm devices, double contact block depth

Empty enclosures

Product	Number of Elements	Catalog Number
Die cast enclosure	One	E34N11
	Two	E34N12
	Three	E34N13
	Four	E34N14
Polyester enclosure	One	E34N51
	Two	E34N52
	Three	E34N53
	Four	E34N54
Stainless steel enclosure	One	10250TN33
	Two	10250TN34
	Three	10250TN35
	Four	10250TN36

Polycarbonate enclosures for 22 mm devices, single and double contact block depth

Empty enclosures

Product	Number of Elements	Catalog Number
Single contact block depth	One	E22CSP1
	Two	E22CSP2
	Three	E22CSP3
	Four	E22CSP4
Double contact block depth	One	E22COP1
	Two	E22COP2
	Three	E22COP3
	Four	E22COP4

10250T 30 mm open components for assembly in empty enclosures (see above)

Pushbuttons

Style	Color	Catalog Number
Non-illuminated momentary flush pushbutton	Black	10250T101
Non-illuminated momentary flush pushbutton	Red	10250T102
Non-illuminated momentary mushroom pushbutton	Black	10250T121
Non-illuminated momentary flush pushbutton with 1NC contacts	Black	10250T101-51
Non-illuminated momentary flush pushbutton with 1NC contacts	Red	10250T102-51

Selector switches

Style	Color	Catalog Number
Two-position non-illuminated knob selector switch 1NO-1NC contacts	Black	10250T20KB
Three-position non-illuminated knob selector switch 2NO contacts	Black	10250T21KB

Legend plates

Legend	Color of Field	Catalog Number
FORWARD	Black	10250TM15
REVERSE	Black	10250TM30
START	Black	10250TM33
STOP	Red	10250TM34
OFF ON	Black	10250TM42
MAN. OFF AUTO	Black	10250TM68

Contact blocks

Circuit	Catalog Number
1NO-1NC	10250T1
2NO	10250T2
2NC	10250T3
1NC	10250T51
1NO	10250T53

E22 22 mm open components for assembly in empty enclosures (see above)

Pushbuttons, chrome bezel

Style	Color	Catalog Number
Non-illuminated momentary extended pushbutton	Red	E22E2
Non-illuminated momentary flush pushbutton	Black	E22P1
Non-illuminated momentary flush pushbutton	Green	E22P3
Non-illuminated momentary mushroom pushbutton	Red	E22L2
Maintained twist-to-release emergency stop operator	Red	E22L12
Maintained trigger-action twist-to-release emergency stop operator	Red	E22LA2
Maintained trigger-action twist-to-release emergency machine off (EMO) operator	Red	E22LA2N123

Legend plates

Legend	Color of Field	Catalog Number
FORWARD	Black	E22NC4
REVERSE	Black	E22NC5
CLOSE	Black	E22NC11
DOWN	Black	E22NC12
OPEN	Black	E22NC26
START	Black	E22NC33
STOP	Black	E22NC34
UP	Black	E22NC35
EMERGENCY STOP	Yellow	E22VA7

Contact blocks

Circuit	Catalog Number
1NC	E22B1
1NO	E22B2
1NO-1NC	E22B11
1NO	E22C1

● For use on trigger-action emergency stop operators.



Assembled stations

Assembled 10250T heavy-duty 30 mm pushbutton control stations, flush mounting

Contact Block(s)	Number of Elements	Type of Elements	Operator Type/Color	Legend	Catalog Number
1NO-1NC	One	Pushbutton	Flush/black	START	10250T3573
1NO-1NC	One	Pushbutton	Head/black	START	10250T3574
1NO-1NC	One	Selector switch	Two-position knob/black	OFF/ON	10250T3580
2NO	One	Selector switch	Three-position knob/black	MAN/OFF/AUTO	10250T3581
1NO-2NC	Two	Pushbutton	Flush/black Flush/red	START STOP	10250T3582
1NO-2NC	Two	Pushbutton	Flush with lock hasp/black Flush with lock hasp/red	START STOP	10250T3599
2NO-2NC	Three	Pushbutton	Flush/black Flush/black Flush/red	FOR REV/STOP	10250T3599

Assembled E22 22 mm pushbutton control stations, chrome bezels

Contact Block(s)	Number of Elements	Type of Elements	Operator Type/Color	Legend	Catalog Number
1NC	One	Pushbutton	Extended/red	STOP	E22AT109
1NC	One	Pushbutton	Flush/green	START	E22AT108
1NC	One	Pushbutton	40 mm latching trigger-action/red	EMERGENCY STOP round yellow nameplate	E22AT111
1NC	One	Pushbutton	40 mm latching trigger-action/red	EMO safety yellow cover	E22AT113
1NO 1NC	Two	Pushbutton	Flush/black Flush/red	START STOP	E22AS204
1NO 1NC	Two	Pushbutton	Flush with lock hasp/black Flush with lock hasp/red	START STOP	E22AS205
1NO 1NC	Two	Pushbutton	Flush with lock hasp/black Flush with lock hasp/red	START STOP	E22AS206
1NO 1NC 1NO	Three	Pushbutton	Flush/black Extended/red Flush/black	FOR STOP REV	E22AS304
1NO 1NC 1NC	Three	Pushbutton	Flush/black Extended/red Flush/black	CLOSE STOP OPEN	E22AS305
1NO 1NC 1NO	Three	Pushbutton	Flush/black Extended/red Flush/black	UP STOP DOWN	E22AS306



10250T 30 mm pilot devices



E22 22 mm pilot devices



22 mm and 30 mm contact blocks



30 mm 10250T knob selector switch



Legend plates