

6 Port USB 3.0 / USB 2.0 Combo Hub with 2A Charging Port – 2x USB 3.0 & 4x USB 2.0

StarTech ID: ST7320USBC



The ST7320USBC 6-Port USB 3.0/2.0 Combo Hub features a special high-output dedicated charging port which enables you to charge USB devices by providing up to 2A of power, or it can add 2x USB 3.0 and 4x USB 2.0 ports to a computer through a single USB 3.0 host connection.

The hub includes an external power adapter, which when connected enables charging some portable electronic devices (e.g. an iPhone® or other Smartphone), even without a USB connection to a host computer.

Offering a unique design that features USB ports along 3 sides of the hub, as well as a combination of USB 2.0 and 3.0 ports, this versatile and flexible USB hub is ideal for both laptop and desktop computers.

The ST7320USBC USB 3.0/2.0 hub is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Add multiple USB 3.0 and USB 2.0 to a computer system to support more device connections
- Charge a Smartphone
- Charging high-powered portable devices (such as tablets) which require special high output USB ports for charging
- Make USB ports that are hard to access more accessible, by being positioning the hub in a convenient location (within cable reach)
- Extend the range of a USB device by having the hub act as a mid-point repeater

Features

- 2x USB 3.0 and 4x USB 2.0 ports that can be all accessed simultaneously
- 2 Amp high output USB Dedicated Charging Port (DCP)
- SuperSpeed USB 3.0 compliant host interface, with support for up to 5 Gbps of data bandwidth

Technical Specifications

Warranty	2 Years
Ports	6
Interface	USB 3.0
Chipset ID	VIA VL810E
External Ports	1 - USB 3.0 B (9 pin; SuperSpeed) Female
External Ports	2 - USB 3.0 A (9 pin; SuperSpeed) Female
External Ports	4 - USB A (4 pin) Female
Type and Rate	USB 2.0 - 480 Mbit/s
Type and Rate	USB 3.0 - 4.8 Gbit/s
OS Compatibility	Windows XP(32/64-bit)/ Server 2003(32/64-bit)/ Vista(32/64-bit)/ Server 2008 R2/ 7(32/64-bit), Mac OS 10.2 ~ 10.6, Linux
Color	Black
Enclosure Type	Plastic
Product Length	99 mm [3.9 in]
Product Width	60 mm [2.4 in]
Product Height	20 mm [0.8 in]
Product Weight	75.4 g [2.7 oz]
LED Indicators	1 - Power
Power Adapter Included	Yes
Input Voltage	110 ~ 240 AC
Output Voltage	5 DC
Output Current	4A
Operating Temperature	0°C to 85°C (32°F to 185°F)
Storage Temperature	-10°C to 95°C (14°F to 203°F)
Humidity	5~90% RH
System and Cable Requirements	Available USB 3.0 or 2.0 port
Package Quantity	1
Shipping (Package) Weight	500 g [17.6 oz]
Included in Package	1 - 6 Port USB Hub
Included in Package	1 - USB 3.0 Cable
Included in Package	1 - Universal Power Adapter
Included in Package	3 - Power Adapter Plug (NA/ EU/ UK)
Included in Package	1 - Instruction Manual

Certifications, Reports and Compatibility

