

1:2 Standalone USB 2.0 Flash Drive Duplicator and Eraser - Flash Drive Copier

StarTech ID: USBDUP12



The USBDUP12 Standalone Flash Drive Duplicator/Eraser offers a quick and easy solution for cloning a USB flash drive to one or two target USB flash drives or erasing up to two thumb drives simultaneously without having to connect the drives to a computer system.

Featuring high performance duplications at up to 1.5GB per minute, the flash drive copier has a lightweight design and user friendly interface that includes an integrated LCD display. The duplicator can copy the entire source drive volume, or for quicker backups just the data on the drive.

In addition, the target USB ports of the duplicator also support connecting to external USB storage devices. The standalone USB duplicator supports copying/cloning to SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media through a USB multimedia card reader (sold separately), and to Hard Drives or Solid State Drives through a Hard Drive docking station or USB enclosure.

The Drive Duplicator also functions as a Flash Drive Eraser capable of erasing up to two USB drives simultaneously with several erase modes available including Quick erase and Full erase, as well as Secure erase, which follows the USA Department of Defense (DoD) secure erase standard, passing over the flash drive 3 times to ensure that the data has been completely wiped.

The USBDUP12 Flash Memory Duplicator is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Quick, hassle-free USB Flash Drive backups, data recovery and drive erasing
- Bit-by-bit Flash Drive imaging/cloning to create an exact replica of a source USB drive onto two target USB drives
- Law enforcement and forensic technicians who need one or more exact copies of the original USB Flash Drive for testing or investigation purposes
- Thoroughly erasing data from a flash drive, for added data security and peace of mind

Features

- Standalone duplicator, no computer required
- Supports USB 2.0/ USB 1.1 Flash Drives
- Choose to copy either data only or the full storage capacity of the USB drive
- Supports both Asynchronous and Synchronous copy modes, with 64MB of internal memory
- High performance duplication at up to 1.5GB/minute
- Check Capacity/Quality/Speed of the connected USB Flash Drive(s)
- Department of Defense (DoD) secure erase
- Instant power on/off allows for quick and easy duplications
- Lightweight, user-friendly design
- Integrated LCD display for duplication progress and options menu
- Supports duplicating to HDD/ SSD/ SD/ SDHC/ Micro SD/ MMC/ Mini SD/ CF media types through a USB enclosure, dock, or multimedia card reader (sold separately)

Technical Specifications

Warranty	2 Years
Buffer Size	64 MB
Bus Type	USB 2.0
Drive Installation	Removable
Drive Type	USB Flash Drive
Number of Drives	3
Drive Connectors	3 - USB A (4 pin) Female
Maximum Data Transfer Rate	1.5GB per minute
Color	Black
Enclosure Type	Plastic
Product Height	25 mm [1 in]
Product Length	120 mm [4.7 in]
Product Weight	190 g [6.7 oz]
Product Width	130 mm [5.1 in]
LED Indicators	3 - Green (Activity/Successful Copy)
LED Indicators	3 - Red (Error)
Center Tip Polarity	Positive
Input Voltage	110 ~ 240 AC
Output Current	2
Output Voltage	5 DC
Plug Type	H
Power Adapter Included	Yes
Humidity	5% ~ 95% RH
Operating Temperature	5°C ~ 45°C (41°F ~ 113°F)
Storage Temperature	-20°C ~ 85°C (-4°F ~ 185°F)
Note	For duplication, the destination drive must be of equal or greater capacity than the source drive.
Package Quantity	1
Included in Package	1 - Duplicator
Included in Package	1 - Universal Power Adapter
Included in Package	3 - Power Adapter Plug (NA/ UK/ EU)
Included in Package	1 - Instruction Manual
Shipping (Package) Weight	550 g [19.4 oz]

Certifications, Reports and Compatibility

