

MCE MCE PC 9 MF/M



Sample photo

Order symbol: MCE PC 9 MF/M
Product nbr: 7219171
Description: DIN rail modular enclosure, PC

EAN: 6418074007599
El. number:
 Finland: 3422203
 Denmark: 8212029017
 Italy: 7740090
 Sweden: 2276234
 Norway: 2537001

Remarks:

Including: Modular component enclosure with TPE gaskets, mounted DIN 35-rail, two PEN 10 mm² bars mounted, Multi-FEM and FEM membrane cable glands, module marking stripe and pocket, wall mount cover plugs and mounting instructions.

Dimensions:		Length	Width	Height	Rating:
mm:		200	190	105	Ingress Protection (EN 60529): IP 65
inch:		7.9	7.5	4.1	Impact Resistance (EN 62262): IK 08
Materials:					Electrical insulation: Totally insulated
Material:		Polycarbonate			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7035			UV resistance: UL 508
Cover colour:		Smoked grey			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Grey			UL Type: UL TYPE 1
Gasket material:		TPE			
Temperatures:					Certificates:
Short term:		-40 ... 120 °C			Fimko
Continuous:		-40 ... 80 °C			Europe EN 62208: 2003
Short term:		-40 ... 250 °F			Gost R
Continuous:		-40 ... 175 °F			
Accessories:					
FP 26128		Fastening lug set			
FP 26127		Fastening lug set			

