

Epson WorkForce WF-3520DWF



The Epson WorkForce WF-3520DWF has been designed to fit perfectly into small, busy office environments with its fast print speeds and duplex printing, scanning, copying and faxing. In addition, this model features a 6.3cm LCD screen with intuitive control panel for easy menu navigation, and Wi-Fi and Ethernet connectivity.

Thanks to Epson's fast drying DURABrite Ultra Ink, business documents are water, smudge and highlighter resistant. Cartridges are also available in XL size, helping to save further on costs. XL inks are ideal for high print volumes, offering up to a 50 percent lower cost-per-page than competitive lasers*1.

Business-quality printing at up to 15ppm for single-sided documents and 7.9ppm for double-sided documents*2, ensure work is delivered quickly and efficiently every time.

This device allows users to load up to 250 sheets of A4 plain paper. It has a single-sheet rear-feed paper tray providing media flexibility, accepting varied paper types and thicknesses, such as card, envelopes and business cards. With a duplex ADF for multi-page scanning, copying and faxing, this printer provides everything a small office or workgroup needs, in one compact device.

Epson Connect*3 allows users to print wirelessly from smartphones and tablet PCs within the office and print from anywhere in the world by emailing documents directly to the printer's unique email address. The Remote Printer Driver offers more flexibility to print from a PC to any Epson Connect printer anywhere in the world, while Scan-to-Cloud enables users to store scanned documents directly in Cloud services. In addition the WF-3520DWF is Apple AirPrint and Google Cloud print ready.

DATASHEET



KEY FEATURES

- Print, scan, copy and fax with ADF
- Print up to 15 pages per minute*2
- Wi-Fi and Ethernet
- 6.3cm LCD screen
- Freedom to print and scan anywhere

PRODUCT SPECIFICATIONS

TECHNOLOGY

Printing Method	4-colour inkjet printer
Nozzle Configuration	384 Nozzles black, 128 Nozzles per colour
Minimum Droplet Size	2 pl, With Variable-Sized Droplet Technology
Ink Technology	Epson DURABrite™ Ultra
Category	Office
All-in-One Functions	Scan, Copy, Fax

PRINT

Printing Speed ISO/IEC 24734	15 Pages/min Monochrome, 9.2 Pages/min Color
Draft printing speed	38 Pages/min Monochrome (plain paper 75 g/m²), 38 Pages/min Color (plain paper 75 g/m²)
Duplex Printing Speed	7.9 A4 Pages/min Monochrome, 5.7 A4 Pages/min Color
ISO/IEC 24734	
Printing Resolution	5,760 x 1,440 dpi
Max Duty cycle	12,000 Pages per month
Colours	Black, Cyan, Yellow, Magenta

For detailed information on printing speeds please visit <http://www.epson.eu/testing>.

SCAN

Scan speed black A4	300 dpi 1.1 msec/line, 600 dpi 1.9 msec/line
Scan speed colour A4	300 dpi 3 msec/line, 600 dpi 5.8 msec/line
Scanning Resolution	1,200 dpi x 2,400 dpi (Horizontal x Vertical)
Scanner type	Contact image sensor (CIS)

FAX

Type of fax	Walk-up black and white and colour fax capability
Error correction mode	CCITT/ITU Group3 fax with Error Correction Mode
Fax speed dials (max)	100 names and numbers
Page memory	Up to 180 pages (ITU-T No.1 chart)
Fax Functions	PC Fax, Memory Reception, Auto Redial, Speed Dial

CONNECTIVITY

Interfaces	Hi-Speed USB - compatible with USB 2.0 specification, Ethernet interface (100 Base-TX / 10 Base-T), Wireless LAN IEEE 802.11b/g/n
WLAN Security	WEP 64 Bit, WEP 128 Bit, WPA PSK (TKIP), WPA PSK (AES)
Mobile and Cloud printing services	Epson Connect (iPrint, Email Print, Remote Print Driver, Scan-to-Cloud), Apple AirPrint, Google Cloud Print

PAPER / MEDIA HANDLING

Paper Formats	A4, A5, A6, B5, C4 (Envelope), C6 (Envelope), DL (Envelope), No. 10 (Envelope), Letter, Letter Legal, 10 x 15 cm, 13 x 18 cm, 16:9, User defined
---------------	--

LOGISTICS INFORMATION

SKU	C11CC33301
Barcode	8715946512754
Dimensions Single Carton	534 x 488 x 328 mm
Carton Weight	11.2 Kg
Country of Origin	Indonesia
Pallet Size Euro	12 Units (2 x 6)
Pallet Size Block	24 Units (4 x 6)



For more information please contact:

Telephone: 0871 222 6702 (UK)+
01 436 7742 (Republic of Ireland)
E-mail: enquiries@epson.co.uk
Chat: etalk.epson-europe.com
Fax: 0871 222 6740

Web: www.epson.co.uk
www.epson.ie

+ Calls cost 10p per minute plus network extras.

Trademarks and registered trademarks are the property of Seiko Epson Corporation or their respective owners. Product information is subject to change without prior notice.

Epson WorkForce WF-3520DWF

WHAT'S IN THE BOX

- Driver and utilities (CD)
- Fax guide
- Individual Ink Cartridges
- Installation/safety manual
- Main unit
- Power cable
- Setup guide
- User manual (CD)
- Warranty document

INK YIELD DATA



Stag T1304

●	765 pages*
●	945 pages*
●	600 pages*
●	1,005 pages*

* Approx. page yield based on ISO/IEC 24711/24712 or ISO/IEC 29102/29103. Actual yield will vary depending on images printed and usage conditions. For more information visit %LINK%

SUPPLIES

- Singlepack Black T1301 DURABrite Ultra Ink C13T13014010 (945 pages)
- Singlepack Cyan T1302 DURABrite Ultra Ink C13T13024010 (765 pages)
- Singlepack Magenta T1303 DURABrite Ultra Ink C13T13034010 (600 pages)
- Singlepack Yellow T1304 DURABrite Ultra Ink C13T13044010 (1,005 pages)
- Multipack 3-colours T1306 DURABrite Ultra Ink C13T13064010
- Singlepack Black T1291 DURABrite Ultra Ink C13T12914011 (385 pages)

1. For more information, please visit www.epson.eu/inkjetsaving
2. Determined in accordance with ISO/IEC 24734 showing the average of ESAT from the Office Category Test for default simplex and duplex. For more information, please visit www.epson.eu/testing
3. Requires a wireless connection to the internet. For more information, supported languages and devices please visit www.epsonconnect.eu
4. For more information, please visit www.epson.eu/testing
5. The maximum number of printed pages per month based on the performance capabilities of the printer, including ISO rated print speeds and paper handling capabilities
6. Adaptor required (not supplied in box)

EPSON®