

Orbital Disc Sanders



Model Number	D26453-GB	DW443	D26410
Input Power	280 W	530 W	400 W
No Load Speed	7000-12000 rpm	4000-7600 rpm	4000-10000 rpm
Base Plate Diameter	125 mm	150 mm	150 mm
Weight	1.6 kg	2.7 kg	2.7 kg

D26453-GB

280W variable speed palm grip sander. Dual-plane counter-balance fan reduces vibration and user fatigue. Dust-sealed switch. Supplied with sanding sheet, fabric dust bag with built-in extractor ports.



	Order Code	Price Each
Voltage 230V	135-2922	

DW443

150mm random orbit sander. Variable speed electronic soft start. Controlled finishing system keeps the pad at a controlled speed. Hook and loop paper system. Supplied with sanding sheets, multi-position side handle and dust bag.



	Order Code	Price Each
Voltage 230V	135-3010	

D26410

400W 150mm random orbit sander. Variable speed for heat sensitive sanding, polishing and superior finishing. The controlled finishing system (CFS) eliminates start up scratching. Integrated dust collection assists in producing a safe working environment and helps to extend sandpaper life. Supplied with sanding sheets, paper dust bag and support tray.



	Order Code	Price Each
Voltage 230V	135-2911	
110V	135-2912	

484131