

Standard Marking of Quarts Crystals

Ver.8
2011/03/10
CITIZEN FINTECH MIYOTA

These are standard marking , available marking digits and the number of lines refer to following a table.

If you need other marking , Please contact us

Model	Standard Marking	Print		Max available marking	
		ink	laser	lines	digits
CFS-308	Sym3	O	×	1	6
CFS-206	Sym1	O	×	1	5
CFS-145	No Mark	×	×		
CFV-206	**ym	O	×	1	5
CM200C	32Cyww	×	O	1	6
CM250C	ffCyww Exception)32kHz: 32Hyww	×	O	1	6
CMR200T	32Cym	×	O	1	5
CMJ206	32Cym	×	O	1	5
CM130	32Cym	×	O	1	5
CM519 CM415	Cym###	×	O	1	6
CM315	ym###	×	O	1	5
CSA-309 CSA-310	f.ffCym or ff.fCym	O	×	1	7
HC-49/U-S HCM49	f.ffCym or ff.fCym	×	O	2	8
CMR-309 CMR-310 (over coat)	f.ffCym or ff.fCym	O	×	1	7
CMR309T CMR310T (over coat)	f.ffCym or ff.fCym	×	O	1	8
CM309S (over coat)	C AAym ff.fffM	O	O	2	8 8
CS20	C AAym ff.fffM	×	O	2	8
CS10	C AAym ff.fff	×	O	2	6
CS325	Cym## ffff	×	O	2	5 (Not include a decimal point and indicate kHz range)

f : frequency kHz range frequency crystal is not available of a decimal point and others

Digit number is included a decimal point

CM309S is available of 8 letters included a decimal point.

CSA-309 and CSA-310 are available of 7 letters included a decimal point.

y : y is 1 figure from the bottom of the Christian era

m : m is product month ,(refer to following table)

month	1 2 3 4 5 6 7 8 9 10 11 12
mark	1 2 3 4 5 6 7 8 9 X Y Z

** : Manufacture's ID code

: our lot number

ww: week code