

Mechanical safety switch PSENmech with guard locking



Safe monitoring of a movable guard with interlock (guard locking) with the mechanical safety switch PSEN me1 with separate actuator.



PSENme 1M / 1AS

Product number: 570004

Type:	PSEN me1
Product version:	2.0
Approvals:	CE, BG, GOST, CCC, cCSAus
Type of guard locking:	Magnetic force
Extraction force:	27 N
Holding force:	1500 N
Auxiliary release:	No
Actuator:	Standard
Number of N/O:	2
Number of N/C:	2
Voltage at AC1:	240 V
Max. current at AC1:	2.5 A
Voltage at AC15:	230 V
Max. current at AC15:	2.5 A
Supply voltage:	24 V
Supply voltage type:	AC/DC
Power consumption AC:	4.4 VA
Power consumption DC:	4.4 W
Protection type, housing:	IP67
Width dimension:	42.5 mm
Height dimension:	184.0 mm
Depth dimension:	51.0 mm
Gross weight:	421 g
Net weight:	361 g

Copyright 2000-2012 Pilz GmbH & Co. KG All rights reserved. All pictures, graphics, texts, sound files, video files and animation files on this website are subject to copyright and/or other laws to protect intellectual property. No data may be copied, amended or used in other publications, whether in electronic or printed format, without the express agreement of Pilz GmbH & Co. KG.