

## Hammer Drills - Cordless



Model Number	DC213KA	DC213KB	DC222KA	DC223KA	DC224KA	DC224KB
Voltage	18 V	18 V	24 V	24 V	24 V	24 V
No Load Speed	1100 rpm	1100 rpm	1100 rpm	1100 rpm	1100 rpm	1100 rpm
Blows/min	0-4200 BPM	0-4200 BPM	0-4200 BPM	0-4200 BPM	0-4200 BPM	0-4200 BPM
Drilling Capacity Steel	13 mm	13 mm	13 mm	13 mm	13 mm	13 mm
Drilling Capacity Wood	30 mm	30 mm	30 mm	30 mm	30 mm	30 mm
Drilling Capacity Concrete	20 mm	20 mm	22 mm	22 mm	22 mm	22 mm
Battery	2 x 2.4Ah Ni-Cd	2 x 3.0Ah Ni-MH	2 x 2.0Ah Ni-Cd	2 x 2.0Ah Ni-Cd	2 x 2.0Ah Ni-Cd	2 x 3.0Ah Ni-MH
Chuck	SDS-Plus	SDS-Plus	SDS-Plus	SDS-Plus	SDS-Plus	SDS-Plus
Weight	3.1 kg	3.1 kg	3.8 kg	3.8 kg	4.0 kg	4.0 kg

### DC213KA



18V heavy duty SDS-Plus 3 mode hammer drill. Variable speed trigger control. Internal mechanism connected to spring dampeners for lower vibration. Supplied with charger, 2 x 2.4Ah Ni Cd battery packs, side handle, grease tube and carrying case.

Description	Order Code	Price Each
DC213KA hammer drill	135-2937	
Replacement battery DE9096	135-2985	

### DC213KB



18V 3-mode SDS-Plus cordless hammer drill. Suitable for drilling anchors and fixing holes in concrete, brick and masonry from 4 to 20mm. Compact design and rear mounted battery for balance and comfort. Internal mechanism connected to external housings via spring dampeners resulting in lower vibration and reduced user fatigue. Impact energy 2.1J. Supplied with charger, 2 x 3.0Ah Ni MH battery packs, grease tube and heavy duty carry case.

Description	Order Code	Price Each
DC213KB hammer drill	135-2938	
Replacement battery DE0241	135-2971	

### DC222KA



24V 2-mode SDS-Plus cordless hammer drill. Suitable for drilling anchors and fixing holes in concrete, brick and masonry from 4 to 22mm. Compact design and rear mounted battery for balance and comfort. Internal mechanism connected to external housings via spring dampeners resulting in lower vibration and reduced user fatigue. Impact energy 2.1J. Supplied with charger, 2 x 2.0Ah Ni Cd battery packs, grease tube and heavy duty carry case.

Description	Order Code	Price Each
DC222KA hammer drill	135-2939	
Replacement battery DE0243	135-2973	

### DC223KA



24V 3 mode SDS-Plus hammer drill. Internal mechanism connected to external housings via spring dampeners meaning significantly lower vibration. Supplied with charger, 2 x 2.0Ah Ni Cd battery packs, side handle, grease and carrying case.

Description	Order Code	Price Each
DC223KA hammer drill	135-2940	
Replacement battery DE0243	135-2973	

### DC224KA



24V 3 mode SDS-Plus hammer drill with quick change chuck. Internal mechanism connected to external housings via spring dampeners meaning significantly lower vibration. Supplied with charger, 2 x 2.0Ah Ni Cd battery packs, side handle, grease and carrying case.



Description	Order Code	Price Each
DC224KA hammer drill	135-2941	
Replacement battery DE0243	135-2973	

**DC224KB**



24V 3 mode SDS-Plus hammer drill with quick change chuck. Internal mechanism connected to external housings via spring dampeners meaning significantly lower vibration. Supplied with charger, 2 x 3.0Ah Ni MH battery packs, side handle, grease and carrying case.

484226

Description	Order Code	Price Each
DC224KB hammer drill	135-2942	
Replacement battery DE0241	135-2971	