



General Purpose Probe (H0234D)

Key Features

- 2046T Plug type connector
- Thermistor sensor
- Straight cable
- 120°C/248°F Maximum tip temperature
- 1.9 time const. (secs)
- 100mm/3.9" shaft length
- 3.3mm/0.15" shaft width (at widest point)

