

FKS-600 & FKS-6000 Precision Weighing Balance



These precision weighing balances have an impact-resistant ABS plastic case and weighing pan, a splash-proof protective cover and non-slip rubber feet. The balance can be either battery or mains powered.

- Weighs in Kg/g or g or lbs/oz or oz.
- Impact-resistant ABS case with non-slip rubber feet
- Splash-proof protective cover
- 175 x 160mm weighing pan
- 20mm Hi-Contrast LCD display with Backlight
- Automatic backlight when weight is added to the pan
- Zero tracking ensures stable and repeatable readings
- Tare facility over the full range and can be actioned several times throughout a weighing cycle
- Plus/Minus weighing
- Low Battery indication
- Auto Power Off after 1.5 minutes of no activity.
- Supplied with user guide and batteries
- 2 year warranty

Technical Specifications

	FKS-600	FKS-6000
Capacity	600g	6,000g
Resolution	0.1g	1g
Accuracy	±0.2g	±2g
Power	6 x 1.5V AAA Alkaline Battery (LR-6) or AC/DC Mains Power Adaptor (not supplied)	
Dimensions	230 x 180 x 50mm (Unit) 175 x 160mm (Pan)	
Weight	0.9Kg	