

FGL-600
Precision Weighing Balance



This precision weighing balance is housed in an impact-resistant ABS case with a 115mm stainless steel weighing pan, splash-proof membrane keypad, levelling bubble and adjustable feet. The balance can be either battery or mains powered via an AC/DC Adaptor.

- Weighs in g, oz, ct & tola
- Impact-resistant ABS case with adjustable feet
- Splash-proof membrane keypad incorporating 3 function keys
- 115mmØ Stainless Steel weighing pan
- 26mm Hi-Contrast LCD display with Backlight
- Automatic backlight when weight is placed on the pan
- Zero tracking ensures stable and repeatable readings
- Tare facility over the full range
- Overload protection to 100% over capacity
- Low Battery indication
- Auto Power Off after 1.5 minutes of no activity (battery powered only)
- Supplied with user guide and battery
- 2 year warranty

Note: Bowl not supplied

Technical Specifications

Capacity	600g
Resolution	0.01g
Accuracy	±0.02g
Power	4 x 1.5V AAA Alkaline Battery (LR-6) or AC/DC Mains Power Adaptor (not supplied)
Dimensions	230 x 180 x 60mm (Unit) 115mmØ (Pan)
Weight	1.5Kg