

Item no.: 250-404
 Product description: 1-CONDUCTOR PCB TERMINAL STRIP 1 SOLDER PIN /
 POLE STAGGERED 4 POLE PIN SPACING 2.5 MM / 0.098 IN
 WITH PUSH BUTTONS WITH TEST SLOT FOR TEST PLUG
 TO 1.3 MM Ø



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	4 (Printed Circuit)
Weight	1.565 g
Color	gray
No. of connection Points	4
No. of potentials	4
pole count	4
Height	13.1 mm
Height	0.516 in
Width	11.5 mm
Width	0.453 in
Depth	12 mm
Depth	0.472 in
Pin spacing from	2.5 mm
Pin spacing from	0.098 in
Pollution degree	2
Measured voltage EN	160 V
Measured shock voltage	2.5 kV

Current intensity EN	4 A
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	4 A



Diameter from	0.4 mm
Diameter to	0.8 mm
Cross section [mm ²]	0.14 - 0.5 mm ²
Wiring method	solid
Cross section [mm ²]	0.2 - 0.5 mm ²
Wiring method	fine-stranded
Cross section to [mm ²]	0.25 mm ²
Wiring method	fine-stranded (with ferrule and plastic collar)
Cross section to [mm ²]	0.25 mm ²
Wiring method	fine-stranded (with ferrule, without plastic collar)
Cross section [AWG]	24 - 20 AWG
Strip length from	8.5 mm
Strip length to	9.5 mm
Material group	I
Contact surface	Copper
xxx-xxx/000-004	black
xxx-xxx/000-005	red
xxx-xxx/000-006	blue
xxx-xxx/000-009	light gray
xxx-xxx/000-012	orange
xxx-xxx/000-024	violet
xxx-xxx/000-050	white



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
250-404	CCA	NL6336	250	6	0,2-1,5
250-404	CSA	154112-1132097	300	2	24-22
250-404	KEMA	2114919.01	250	6	0,2-1,5
250-404	RMR	11130002	250	2	0,5-1,5
250-404	UR	E45172	300	5	26-20

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected