

## Angle Head Drills - Cordless



### DW965K



12V heavy duty 10mm cordless right angle drill. Dual speed gearbox with reverse action. Multiple grip soft touch switch. Keyless chuck with electronic brake. Supplied with charger, 1 x 2.0Ah Ni Cd battery pack and carrying case.

Model Number	DW965K
Voltage	12.0 V
No Load Speed	0-400/0-1200 rpm
Drilling Capacity Steel	10 mm
Drilling Capacity Wood	25 mm
Battery	1 x 2.0Ah Ni Cd
Chuck Capacity	10mm
Weight	2.0 kg

Description	Order Code	Price Each
DW965K drill	<b>135-3031</b>	
Replacement battery DE9071	<b>135-2976</b>	

### DW966K



14.4V, heavy duty 10mm cordless right angle drill. Dual speed gearbox with reverse action. Multiple grip soft touch switch. Keyless chuck with electronic brake. Supplied with charger, 1 x 2.0Ah Ni Cd battery pack and carrying case.

Model Number	DW966K
Voltage	14.4 V
No Load Speed	0-400/0-1250 rpm
Drilling Capacity Steel	10 mm
Drilling Capacity Wood	28 mm
Battery	1 x 2.0Ah Ni Cd
Chuck Capacity	10mm
Weight	2.1 kg

Description	Order Code	Price Each
DW966K drill	<b>135-3033</b>	
Replacement battery DE9091	<b>135-2979</b>	

484818