

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [53047-1010](#)
Status: **Active**
Overview: [PicoBlade™](#)
Description: 1.25mm Pitch PicoBlade™ Wire-to-Board Header, Vertical, with Friction Lock, 10 Circuits

Documents:

[3D Model](#) [Packaging Specification SPK-53047-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-51021-010 \(PDF\)](#)

Agency Certification

UL E29179

General

Product Family PCB Headers
 Series [53047](#)
 Application Signal, Wire-to-Board
 Overview [PicoBlade™](#)
 Product Name PicoBlade™
 UPC 800753565852

Physical

Breakaway No
 Circuits (Loaded) 10
 Circuits (maximum) 10
 Durability (mating cycles max) 30
 First Mate / Last Break No
 Flammability 94V-0
 Glow-Wire Compliant No
 Guide to Mating Part No
 Keying to Mating Part None
 Lock to Mating Part Yes
 Mated Height 5.20mm
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 200.200/mg
 Number of Rows 1
 Orientation Vertical
 PC Tail Length 2.30mm
 PCB Locator No
 PCB Retention None
 PCB Thickness - Recommended 0.80mm
 Packaging Type Tray
 Pitch - Mating Interface 1.25mm
 Polarized to PCB No
 Shrouded Fully
 Stackable No
 Surface Mount Compatible (SMC) No
 Temperature Range - Operating -40°C to +85°C
 Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 1A
 Voltage - Maximum 125V

Material Info




image - Reference only

Series

EU RoHS

ELV and RoHS Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[53047Series](#)

Mates With

[51021 PicoBlade™ Wire-to-Wire](#)

Reference - Drawing Numbers

Packaging Specification
Product Specification

SPK-53047-001
PS-51021-010, RPS-51021-007, RPS-51021-011,
RPS-51021-019, RPS-51021-041, RPS-51021-059,
RPS-51021-060, RPS-51021-071, RPS-51021-089,
RPS-51021-104
SD-53047-**10

Sales Drawing

This document was generated on 07/24/2013

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION