

## Ferrite shallow pot magnets

Max. operating temperature 120°C.

Mild steel pot.

Zinc plated.



Product No.	Diameter mm	Height	Weight kg	Pull force	Units / pack
E700	10	4.5	0.002	0.4	20
E701	13	4.5	0.003	1.0	20
E702	16	4.5	0.0045	1.8	20
E703	20	6	0.010	3.0	10
E704	25	7	0.019	4.0	10
E705	32	7	0.030	8.0	10
E706	40	8	0.055	12.5	5
E707	50	10	0.100	22.0	5
E708	63	14	0.230	35.0	1
E709	80	18	0.485	60.0	1

## Ferrite hook magnets

Max. operating temperature 120°C.

Mild steel pot. Painted white.

See also neodymium hook magnets on p6 (35kg pull).



Product No.	Diameter	Pot height mm	Total height	Thread size	Weight kg	Pull force	Units / pack
E879-RB	25	8	34	M4	0.027	4.0	1
E880-RB	32	8	34	M4	0.034	8.0	1
E881-RB	36	8	34	M4	0.038	10.0	1

## Ferrite shallow pot magnets Threaded hole

Max. operating temperature 120°C.

Mild steel pot.

Zinc plated.

Female thread



Product No.	Diameter	Pot height mm	Total height	Thread size	Weight kg	Pull force	Units / pack
E860	10	4.5	11	M3	0.003	0.4	20
E861	13	4.5	11.5	M3	0.005	1.0	20
E862	16	4.5	11.5	M3	0.006	1.8	20
E863	20	6	13	M3	0.011	3.0	10
E864	25	7	15	M4	0.022	4.0	10
E865	32	7	15	M4	0.032	8.0	5
E866	36	8	16	M4	0.045	10.0	5
E867	40	8	18	M5	0.060	12.5	5
E868	47	9	17	M4	0.090	18.0	1
E869	50	10	22	M6	0.110	22.0	1
E870	57	10.5	18.5	M4	0.145	28.0	1
E871	63	14	30	M8	0.240	35.0	1
E872	80	18	34	M10	0.520	60.0	1
E873	90	20	40	M10	0.820	70.0	1
E874	100	22	42	M12	0.940	90.0	1
E875	125	26	50	M14	1.720	130.0	1

## Ferrite shallow pot magnets Threaded hole

Max. operating temperature 120°C.

Mild steel pot. Painted red.



Product No.	Diameter mm	Height	Thread	Weight kg	Pull force	Units / pack
E780	50	10	M8	0.16	15	1
E781	80	18	M10	0.56	55	1

## Ferrite shallow pot magnets

Max. operating temperature 120°C.

Mild steel pot with removable hook.

Painted red.



Product No.	Diameter mm	Height	Thread Size	Weight kg	Pull force	Units / pack
E890	46	10.7	M6	0.090	6	5
E891	56	10.7	M6	0.130	16	5
E892	66	10.7	M6	0.190	25	5

As above with three M6 tapped holes to aid mounting products.



Product No.	Diameter mm	Height	Fixing stud centres PCD M6	Central fixing point	Weight kg	Pull force	Units / pack
E895	66	10.7	46mm - 3 holes	M6	0.270	25	1
E896	76	12.5	46mm - 3 holes	M6	0.300	33	1
E897	100	15.5	70mm - 3 holes	M6	0.610	55	1

## Ferrite channel magnets

Max. operating temperature 120°C.

Mild steel body.

Painted red.



Product No.	Length	Width	Height mm	Plain fixing holes	Hole centres	Weight (each) kg	Pull force	Units / pack
E898/1	115	30	13	4.2	80	0.25	8	5
E898/2	130	30	13	4.2	90	0.3	14	5
E899	190	43	13	4.2	110	0.55	48	2