

# Extended-Distance Data Cable, Office Environment, PVC Jacket, 4 Conductors (2 Pairs), 500-ft. (152.4-m)

---

MFG Part Number: EDN04A-0500



## Description

Extended-Distance Data Cable, Office Environment, PVC Jacket, 4 Conductors (2 Pairs), 500-ft. (152.4-m)

## Quick Facts

- For use with RS-232, V.35, RS-422, and RS-485 interfaces.
- Distances up to 500 feet (152.4 m).
- Low capacitance, foil shielded. Ideal choice for office environments.
- 24 AWG stranded construction.
- Guaranteed for life!

## Technical Specifications for Extended-Distance Data Cable, Office Environment, PVC Jacket, 4 Conductors (2 Pairs), 500-ft. (152.4-m):

- **Cable Type** — Twisted pair, PVC jacket
- **Capacitance** — 12 pF/ft.  $\pm$  2 pF/ft.
- **Conductor Gauge** — 24 AWG (7 x 32 AWG) stranded
- **Resistance** — 25 ohms/1000 ft.
- **Shield** — Foil wrap with drain wire