

# Bulk Extended-Distance/Quiet Cable—Industrial Environment, PVC Jacket, 7 Conductors (3 1/2 Pairs), 500-ft. (152.4-m)

---

MFG Part Number: EMN07A-0500



## Description

Bulk Extended-Distance/Quiet Cable—Industrial Environment, PVC Jacket, 7 Conductors (3 1/2 Pairs), 500-ft. (152.4-m)

## Quick Facts

- Low capacitance, braided foil shield.
- 24 AWG stranded construction.
- Guaranteed for life!

## Further Details

Ideal for noisy environments where cable runs are next to power lines and other cabling systems that cause interference.

## Technical Specifications

**Cable Type** — Twisted pair, PVC jacket

**Capacitance** — 12 pF/ft.  $\pm$  2 pF/ft.

**Conductor Gauge** — 24 AWG (7 x 32 AWG) stranded

**Resistance** — 25 ohms/1000 ft.

**Shield** — One foil and one copper braid