

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [87439-0800](#)  
**Status:** **Active**  
**Overview:** [Pico-Spox™](#)  
**Description:** 1.50mm Pitch Pico-SPOX™ Wire-to-Board Housing, 8 Circuits, Off-White Housing

**Documents:**

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#) [Product Literature \(PDF\)](#)  
[Product Specification PS-87437 \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E29179

**General**

Product Family Crimp Housings  
 Series [87439](#)  
 Application Signal, Wire-to-Board  
 MolexKits Yes  
 Overview [Pico-Spox™](#)  
 Product Literature Order No USA-235  
 Product Name Pico-SPOX™  
 UPC 800754313278

**Physical**

Circuits (maximum) 8  
 Color - Resin Natural  
 Flammability 94V-0  
 Gender Female  
 Glow-Wire Compliant No  
 Lock to Mating Part Yes  
 Material - Resin Nylon  
 Net Weight 0.120/g  
 Number of Rows 1  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 1.50mm  
 Polarized to Mating Part Yes  
 Stackable No  
 Temperature Range - Operating -55°C to +105°C


**Electrical**

Current - Maximum per Contact 2.5A

**Material Info**

**Reference - Drawing Numbers**

Product Specification PS-87437, RPS-87437, RPS-87437-001,  
 RPS-87437-200  
 Sales Drawing SD-87439-\*\*00



**EU RoHS**

**ELV and RoHS  
 Compliant**  
**REACH SVHC  
 Contains SVHC: No**  
**Low-Halogen Status  
 Low-Halogen**

**China RoHS**



**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

[87439Series](#)

**Mates With**

Pico-SPOX™ Wire-to-Board Header [87437](#) ,  
[87438](#)

**Use With**

[87421](#) Pico-SPOX™ Crimp Terminal