

Twist drills DIN 338 type N
HSS rolled, HSS ground, HSS Co 5 ground and HSS-TiN ground

Ø mm	Total length mm	Flute length mm	Article no. HSS-R	Cont. pcs.	Article no. HSS-G	Cont. pcs.	Article no. HSS-G Co 5	Cont. pcs.	Article no. HSS-G TiN	Cont. pcs.
0,30	19,0	3,0	201 003	10	214 003	10	—	—	250 003 T	10
0,40	20,0	5,0	201 004	10	214 004	10	—	—	250 004 T	10
0,50	22,0	6,0	201 005	10	214 005	10	—	—	250 005 T	10
0,60	24,0	7,0	201 006	10	214 006	10	—	—	250 006 T	10
0,70	28,0	9,0	201 007	10	214 007	10	—	—	250 007 T	10
0,80	30,0	10,0	201 008	10	214 008	10	—	—	250 008 T	10
0,90	32,0	11,0	201 009	10	214 009	10	—	—	250 009 T	10
1,00	34,0	12,0	201 010	10	214 010	10	215 010	10	250 010 T	10
1,10	36,0	14,0	201 011	10	214 011	10	215 011	10	250 011 T	10
1,20	38,0	16,0	201 012	10	214 012	10	215 012	10	250 012 T	10
1,25	38,0	16,0	201 0125	10	214 0125	10	215 0125	10	250 0125 T	10
1,30	38,0	16,0	201 013	10	214 013	10	215 013	10	250 013 T	10
1,40	40,0	18,0	201 014	10	214 014	10	215 014	10	250 014 T	10
1,50	40,0	18,0	201 015	10	214 015	10	215 015	10	250 015 T	10
1,60	43,0	20,0	201 016	10	214 016	10	215 016	10	250 016 T	10
1,70	43,0	20,0	201 017	10	214 017	10	215 017	10	250 017 T	10
1,75	46,0	22,0	201 0175	10	214 0175	10	215 0175	10	250 0175 T	10
1,80	46,0	22,0	201 018	10	214 018	10	215 018	10	250 018 T	10
1,90	46,0	22,0	201 019	10	214 019	10	215 019	10	250 019 T	10
2,00	49,0	24,0	201 020	10	214 020	10	215 020	10	250 020 T	10
2,10	49,0	24,0	201 021	10	214 021	10	215 021	10	250 021 T	10
2,20	53,0	27,0	201 022	10	214 022	10	215 022	10	250 022 T	10
2,25	53,0	27,0	201 0225	10	214 0225	10	215 0225	10	250 0225 T	10
2,30	53,0	27,0	201 023	10	214 023	10	215 023	10	250 023 T	10
2,40	57,0	30,0	201 024	10	214 024	10	215 024	10	250 024 T	10
2,50	57,0	30,0	201 025	10	214 025	10	215 025	10	250 025 T	10
2,60	57,0	30,0	201 026	10	214 026	10	215 026	10	250 026 T	10
2,70	61,0	33,0	201 027	10	214 027	10	215 027	10	250 027 T	10
2,75	61,0	33,0	201 0275	10	214 0275	10	215 0275	10	250 0275 T	10
2,80	61,0	33,0	201 028	10	214 028	10	215 028	10	250 028 T	10
2,90	61,0	33,0	201 029	10	214 029	10	215 029	10	250 029 T	10
3,00	61,0	33,0	201 030	10	214 030	10	215 030	10	250 030 T	10
3,10	65,0	36,0	201 031	10	214 031	10	215 031	10	250 031 T	10
3,20	65,0	36,0	201 032	10	214 032	10	215 032	10	250 032 T	10
3,25	65,0	36,0	201 0325	10	214 0325	10	215 0325	10	250 0325 T	10
3,30	65,0	36,0	201 033	10	214 033	10	215 033	10	250 033 T	10
3,40	70,0	39,0	201 034	10	214 034	10	215 034	10	250 034 T	10
3,50	70,0	39,0	201 035	10	214 035	10	215 035	10	250 035 T	10
3,60	70,0	39,0	201 036	10	214 036	10	215 036	10	250 036 T	10
3,70	70,0	39,0	201 037	10	214 037	10	215 037	10	250 037 T	10
3,75	70,0	39,0	201 0375	10	214 0375	10	215 0375	10	250 0375 T	10
3,80	75,0	43,0	201 038	10	214 038	10	215 038	10	250 038 T	10
3,90	75,0	43,0	201 039	10	214 039	10	215 039	10	250 039 T	10
4,00	75,0	43,0	201 040	10	214 040	10	215 040	10	250 040 T	10
4,10	75,0	43,0	201 041	10	214 041	10	215 041	10	250 041 T	10
4,20	75,0	43,0	201 042	10	214 042	10	215 042	10	250 042 T	10
4,25	75,0	43,0	201 0425	10	214 0425	10	215 0425	10	250 0425 T	10
4,30	80,0	47,0	201 043	10	214 043	10	215 043	10	250 043 T	10
4,40	80,0	47,0	201 044	10	214 044	10	215 044	10	250 044 T	10
4,50	80,0	47,0	201 045	10	214 045	10	215 045	10	250 045 T	10
4,60	80,0	47,0	201 046	10	214 046	10	215 046	10	250 046 T	10
4,70	80,0	47,0	201 047	10	214 047	10	215 047	10	250 047 T	10
4,75	80,0	47,0	201 0475	10	214 0475	10	215 0475	10	250 0475 T	10
4,80	86,0	52,0	201 048	10	214 048	10	215 048	10	250 048 T	10
4,90	86,0	52,0	201 049	10	214 049	10	215 049	10	250 049 T	10
5,00	86,0	52,0	201 050	10	214 050	10	215 050	10	250 050 T	10
5,10	86,0	52,0	201 051	10	214 051	10	215 051	10	250 051 T	10
5,20	86,0	52,0	201 052	10	214 052	10	215 052	10	250 052 T	10
5,25	86,0	52,0	201 0525	10	214 0525	10	215 0525	10	250 0525 T	10
5,30	86,0	52,0	201 053	10	214 053	10	215 053	10	250 053 T	10
5,40	93,0	57,0	201 054	10	214 054	10	215 054	10	250 054 T	10
5,50	93,0	57,0	201 055	10	214 055	10	215 055	10	250 055 T	10
5,60	93,0	57,0	201 056	10	214 056	10	215 056	10	250 056 T	10
5,70	93,0	57,0	201 057	10	214 057	10	215 057	10	250 057 T	10